



# MASTERCoulour CDM-T

## MASTERC CDM-T 70W/942 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G12 [G12]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	12,000 hour(s)

Light Technical	
Color Code	942 [CCT of 4200K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.377
Chromaticity Coordinate Y (Nom)	0.376
Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	85 lm/W
Color rendering index (CRI)	92

Arc Length O (Nom)	6 mm
--------------------	------

Operating and Electrical	
Power Consumption	73.2 W
Voltage (Nom)	88 V
Voltage (Nom)	88 V

Controls and Dimming	
Dimmable	No


Mechanical and Housing	
Bulb Finish	Clear

# MASTERC colour CDM-T

Bulb Shape	T19 [T 19mm]
<b>Approval and Application</b>	
Mercury (Hg) Content (Nom)	6.1 mg
Energy Consumption kWh/1000 h	80 kWh
<b>Product Data</b>	
Order product name	MASTERC CDM-T 70W/942 G12 1CT/12
Full product name	MASTERC CDM-T 70W/942 G12 1CT/12


Full product code	871869648449400
Order code	928084505129
Material Nr. (12NC)	928084505129
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696484494
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696484500

## Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 70W/942 G12 1CT/12	20 mm	0.75 inch	6 mm	55 mm	57 mm	56 mm	103 mm

## Photometric data





Spectral Power Distribution Colour - MASTERC CDM-T 70W/942 G12 1CT/12

Light Distribution Diagram - MASTERC CDM-T 70W/942 G12 1CT/12

# MASTERC colour CDM-T

## Lifetime



Life Expectancy Diagram - MASTER CDM-T 70W/942 G12 1CT/12

Lumen Maintenance Diagram - MASTER CDM-T 70W/942 G12 1CT/12

