



# SOX

## SOX Plus 55W BY22d T50 1SL/12


Low Pressure Sodium lamp

### Product data

General Information	
Cap base	BY22D [BY22d]
Operating position	H110 [Hanging +/-110D or Base Up (BU)]
Life to 50% failures (nom.)	18,000 h
Light Technical	
Correlated Colour Temperature	1800 K
Luminous efficacy (rated) (nom.)	140 lm/W
Operating and Electrical	
Power Consumption	56.0 W
Lamp current (nom.)	0.51 A
Voltage (nom.)	109 V
Voltage (nom.)	109 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb shape	T50 [T 50 mm]


Approval and Application	
Mercury (Hg) content (nom.)	0 mg
Energy consumption kWh/1,000 hours	64 kWh
Product Data	
Order product name	SOX 55W BY22d T50 1SL/12
Full product name	SOX Plus 55W BY22d T50 1SL/12
Full EOC	871150019471815
Order code	19471815
Material no. (12 NC)	928146000018
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500194718
Numerator – packs per outer box	12
EAN/UPC – Case	8711500194725

Dimensional drawing




Product	D (max)	C (max)
SOX 55W BY22d T50 1SL/12	52 mm	425 mm

Photometric data




Spectral Power Distribution Colour - SOX 55W BY22d T50 1SL/12

Lifetime



Life Expectancy Diagram - SOX 55W BY22d T50 1SL/12



Lumen Maintenance Diagram - SOX 55W BY22d T50 1SL/12

