



Pulse Start Metal Halide Protected

MP400/BU/PS 6PK

Philips Protected Pulse Start Metal Halide "O" Rated Lamps are a better alternative to the standard switch start metal halide.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information		Operating and Electrical	
Cap-Base	EX39 [Exclusionary Mogul Screw]	Lamp Current (Nom)	3.25 A
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]	Voltage (Nom)	135 V
Life to 50% Failures (Nom)	20,000 hour(s)	Voltage (Nom)	135 V
Light Technical		Mechanical and Housing	
Color Code	635 [CCT of 3500K]	Bulb Finish	Clear
Color Designation	White (WH)	Bulb Material	Hard Glass
Chromaticity Coordinate X (Nom)	405	Bulb Shape	ED37
Chromaticity Coordinate Y (Nom)	398		
Correlated Color Temperature (Nom)	3800 K	Approval and Application	
Luminous Efficacy (Rated) (Min)	95 lm/W	Mercury (Hg) Content (Nom)	50 mg
Luminous Efficacy (rated) (Nom)	100 lm/W		
Color rendering index (CRI)	65	Product Data	
		Order product name	MP400/BU/PS 6PK
		Full product name	MP400/BU/PS 6PK

Pulse Start Metal Halide Protected

Order code	928601158102
Material Nr. (12NC)	928601158102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677133344

Numerator - Packs per outer box	6
EAN/UPC - Case	50046677133349

Dimensional drawing



Product	D	C (max)
MP400/BU/PS 6PK	4.625 inch	11.5 inch

