



MASTER LEDtube EM/ Mains T8

MAS LEDtube STD 1200mm 10.5W865 T8 I

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime ensure this tube masters every demanding application.

Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	1,600 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	152.00 lm/W

Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	10.5 W
Lamp Current (Max)	55 mA
Lamp Current (Min)	45 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9

MASTER LEDtube EM/Mains T8

Voltage (Nom)	220-240 V
---------------	-----------

Temperature

Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	35 °C

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	1,200 mm
Bulb Shape	T8

Approval and Application


Energy Saving Product	Yes
-----------------------	-----

Approval Marks	RoHS compliance
Energy Consumption kWh/1000 h	11 kWh

Product Data


Order product name	MAS LEDtube STD 1200mm 10.5W865 T8 I
Full product name	MAS LEDtube STD 1200mm 10.5W865 T8 I
Full product code	871869668770300
Order code	929001297708
Material Nr. (12NC)	929001297708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696687703
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696687710

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube STD 1200mm 10.5W865 T8 I	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Photometric data



General uniform lighting - MAS LEDtube STD 1200mm 10.5W865 T8 I

MASTER LEDtube EM/Mains T8

