



SceneSwitch LEDspot

LEDSSW 4.5-50W GU10 827 36D 1BC/3

Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LEDspot, you can have different light settings from just one spot. And you don't need a dimmer! Optimize your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

Product data

| General Information | |
|---------------------------------------|--|
| Cap-Base | GU10 [GU10] |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 827/825/822 [CCT of 2700K/2500K/2200K] |
| Beam Angle (Nom) | 36 degree(s) |
| Luminous Flux | 390 lm |
| Color Designation | Warm/Extra Warm/Very Warm |
| Luminous Efficacy (rated) (Nom) | 69.00 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 1.5 3.5 5 W |
| Lamp Current (Nom) | 43 mA |


| Starting Time (Nom) | 0.5 s |
|-------------------------------|-----------------------------------|
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.5 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case Maximum (Nom) | 80 °C |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Shape | PAR16 [PAR 2 inch/50mm] |
| Approval and Application | |
| Suitable For Accent Lighting | Yes |
| Energy Consumption kWh/1000 h | 5 kWh |
| Product Data | |
| Order product name | LEDSSW 4.5-50W GU10 827 36D 1BC/3 |
| Full product name | LEDSSW 4.5-50W GU10 827 36D 1BC/3 |
| Full product code | 871869671099900 |

SceneSwitch LEDspot

| | |
|-------------------------------|---------------|
| Order code | 929001346019 |
| Material Nr. (12NC) | 929001346019 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696710999 |


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 3 |
| EAN/UPC - Case | 8718696711002 |

Dimensional drawing




| Product | D | C |
|-----------------------------------|-------|-------|
| LEDSSW 4.5-50W GU10 827 36D 1BC/3 | 50 mm | 54 mm |

Photometric data




Spotlight Parameters 01 Photometry 01 Page 10



Accent Lighting Spots - LEDSSW 4.5-50W GU10 827 36D 1BC/3



Light Distribution Diagram - LEDSSW 4.5-50W GU10 827 36D 1BC/3



Spectral Power Distribution Colour - LEDSSW 4.5-50W GU10 827 36D 1BC/3

SceneSwitch LEDspot

Lifetime



Life Expectancy Diagram - LEDSSW 4.5-50W GU10 827 36D 1BC/3

Lumen Maintenance Diagram - LEDSSW 4.5-50W GU10 827 36D 1BC/3

