



# MASTER LEDspot ExpertColor MV

## MASTER LED ExpertColor 5.5-50W GU10 930 25D

MASTER LEDspot MV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates ambience with superior lighting that has a customised spectrum, high CRI and deep dimming features. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot LV lamps.

### Product data

| General Information        |             |
|----------------------------|-------------|
| Cap base                   | GU10        |
| Nominal lifetime           | 40,000 h    |
| Switching Cycle            | 50,000      |
| Lighting Technology        | LED         |
| Flux measurement reference | Narrow Cone |
| CE mark                    | Yes         |
| EU RoHS compliant          | Yes         |

| Light Technical                  |                    |
|----------------------------------|--------------------|
| Colour Code                      | 930 [CCT of 3000K] |
| Beam angle (nom.)                | 25 degree(s)       |
| Luminous Flux                    | 375 lm             |
| Luminous intensity (nom.)        | 1,000 cd           |
| Colour designation               | White (WH)         |
| Correlated Colour Temperature    | 3000 K             |
| Luminous efficacy (rated) (nom.) | 68.00 lm/W         |
| Colour consistency               | <3                 |

|  |        |
|--|--------|
| Colour rendering index (CRI)                 | 97     |
| LLMF at end of nominal lifetime (nom.)       | 70 %   |
| Luminous flux in 90° cone (rated)            | 375 lm |
| Flickering value (PstLM)                     | 1      |
| Stroboscopic effect                          | 0.4    |
| Photobiological safety according to EN 62471 | RG1    |

| Operating and Electrical  |             |
|---------------------------|-------------|
| Line Frequency            | 50 to 60 Hz |
| Input frequency           | 50 to 60 Hz |
| Power Consumption         | 5.5 W       |
| Lamp current (nom.)       | 30 mA       |
| Wattage equivalent        | 50 W        |
| Starting time (nom.)      | 0.5 s       |
| Warm-up time to 60% light | 0.5 s       |
| Power Factor (Fraction)   | 0.8         |
| Voltage (nom.)            | 220-240 V   |

# MASTER LEDspot ExpertColor MV

## Temperature

|                       |       |
|-----------------------|-------|
| T-Case maximum (nom.) | 80 °C |
|-----------------------|-------|

## Controls and Dimming

|          |                            |
|----------|----------------------------|
| Dimmable | Only with specific dimmers |
|----------|----------------------------|

## Mechanical and Housing

|             |       |
|-------------|-------|
| Lamp Finish | Clear |
| Bulb shape  | PAR16 |

## Approval and Application

|                                    |        |
|------------------------------------|--------|
| Energy Efficiency Class            | G      |
| Suitable for accent lighting       | Yes    |
| Energy consumption kWh/1,000 hours | 6 kWh  |
| EPREL registration number          | 391832 |
| EyeComfort                         | Yes    |


## Application Conditions

|                                     |    |
|-------------------------------------|----|
| Can it be used in closed luminaires | No |
|-------------------------------------|----|

## Product Data


|                                   |   |
|-----------------------------------|---|
| Order product name                | MAS LED ExpertColor 5.5-50W GU10 930 25D    |
| Full product name                 | MASTER LED ExpertColor 5.5-50W GU10 930 25D |
| Full EOC                          | 871869670763000                             |
| Order code                        | 70763000                                    |
| Material no. (12 NC)              | 929001347102                                |
| SAP numerator – quantity per pack | 1   |
| EAN/UPC – Product/Case            | 8718696707630                               |
| Numerator – packs per outer box   | 10  |
| EAN/UPC - Case                    | 8718696707647                               |

## Dimensional drawing




| Product                                  | D     | C     |
|--|-------|-------|
| MAS LED ExpertColor 5.5-50W GU10 930 25D | 50 mm | 54 mm |

## Photometric data



Product Reference: 11 Photo Lighting: 11 Page: 11




Accent Lighting Spots - MAS LED ExpertColor 5.5-50W GU10 930 25D

Spectral Power Distribution Colour - MAS LED ExpertColor 5.5-50W GU10 930 25D


# MASTER LEDspot ExpertColor MV

## Photometric data




Light Distribution Diagram - MAS LED ExpertColor 5.5-50W GU10 930 25D

## Lifetime



Life Expectancy Diagram - MAS LED ExpertColor 5.5-50W GU10 930 25D



Lumen Maintenance Diagram - MAS LED ExpertColor 5.5-50W GU10 930 25D

