



MASTER VALUE LEDspot MV

Master LED 4.9-50W GU10 927 36D Dim

MASTER VALUE 可提供如同卤素灯般的重点照明暖光束，是聚光照明的理想之选。本产品具有高 CRI，光色更为自然，可为住宅和酒店项目营造温馨舒适的氛围，突显零售商品的独特美感。此 LED MV GU10 射灯采用与普通射灯类似的外观和质感，既保留了玻璃射灯的经典美感，又增添了强大的 LED 技术性能。调光功能可以营造理想的舒心氛围，并可兼容多种调光器。MASTER VALUE 的节能效果比普通 LED 射灯更为出众。

产品数据

一般信息	
底盖	GU10
标称使用寿命	25,000 小时
切换循环	50,000
照明技术	LED
符合欧盟 RoHS 规范	是
灯技术	
颜色代码	927
光束角度 (标称)	36 °
光通量	395 lm
发光强度 (标称)	650 cd
颜色名称	暖白色 (WW)
相关色温 (标称)	2700 K
光效 (额定) (标称)	80.61 lm/W
颜色一致性	<6
显色指数 (CRI)	90
标称使用寿命结束时灯的光通维持率 (标称)	70 %
90° 圆锥形光通量 (额定)	355 lm

操作和电气	
频率	50 to 60 Hz
输入频率	50 至 60 Hz
功耗	5 W
灯具电流 (标称)	27 mA
瓦数相当	50 W
启动时间 (标称)	0.5 s
60% 灯光下的预热时间	0.5 s
功率系数 (小数)	0.8
电压 (标称)	220-240 V
温度	
最大外壳温度 (标称)	80 °C
控制和调光	
可调光	是
机械和外壳	
灯泡外形	PAR16 [PAR 2 英寸/50 毫米]


MASTER VALUE LEDspot MV

审批和申请	
适用于重点照明	是
能耗 kWh/1000 h	5 kWh
EyeComfort	是

产品数据	
订单产品名称	Master LED 4.9-50W GU10 927 36D Dim
完整的产品名称	Master LED 4.9-50W GU10 927 36D Dim
完整产品代码	871869670731900



订购代码	929001348808
材料编号 (12NC)	929001348808
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718696707319
计算器 - 每个外包装箱中的包数	10
EAN/UPC - 案例	8718696707326

二维绘图



Product	D	C
Master LED 4.9-50W GU10 927 36D Dim	50 mm	54 mm

光度数据




Accent Lighting Spots – Master LED 4.9-50W GU10 927 36D Dim

Spectral Power Distribution Colour – Master LED 4.9-50W GU10 927 36D Dim


MASTER VALUE LEDspot MV

光度数据




Light Distribution Diagram - Master LED 4.9-50W GU10 927 36D Dim

寿命



Life Expectancy Diagram - Master LED 4.9-50W GU10 927 36D Dim



Lumen Maintenance Diagram - Master LED 4.9-50W GU10 927 36D Dim

