



TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

TForce LED HPI ND 110-88W E40 840 120D

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in Highbay application. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus they come for a low initial investment. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour rendering index enhance the lighting distribution while creating a comfortable, safe and high productivity environment.

Warnings and Safety

• EM version requires an EM ballast to operate. Please refer to the installation guide or consult a Philips Lighting representative.

Product data

General Information		Luminous Flux	
Cap-Base	E40 [E40]	11,000 lm	
Nominal lifetime	50,000 hour(s)	Color Designation	
Switching Cycle	50,000	Cool White (CW)	
Lighting Technology	LED	Correlated Color Temperature (Nom)	
EU RoHS compliant	Yes	4000 K	
Light Technical		Luminous Efficacy (rated) (Nom)	
Color Code	840 [CCT of 4000K]	125.00 lm/W	
Beam Angle (Nom)	120 degree(s)	Color Consistency	
		<6	
		Color rendering index (CRI)	
		80	
		LLMF At End Of Nominal Lifetime (Nom)	
		70 %	
		Operating and Electrical	
		Line Frequency	
		50 Hz	

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Input Frequency	50 Hz
Power Consumption	88 W
Lamp Current (Nom)	2,500 mA
Starting Time (Nom)	1.2 s
Warm-up time to 60% light	1.2 s
Power Factor (Fraction)	0.7
Voltage (Nom)	100-145 V

Temperature

T-Case Maximum (Nom)	90 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Shape	Others
------------	--------


Approval and Application

Energy Consumption kWh/1000 h	97 kWh
-------------------------------	--------

Product Data


Order product name	TForce LED HPI ND 110-88W E40 840 120D
Full product name	TForce LED HPI ND 110-88W E40 840 120D
Full product code	871869671382200
Order code	929001356902
Material Nr. (12NC)	929001356902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696713822
Numerator - Packs per outer box	2
EAN/UPC - Case	8718696713839

Dimensional drawing




Product	D	C
TForce LED HPI ND 110-88W E40 840 120D	210 mm	250 mm

Photometric data




Spectral Power Distribution Colour - TForce LED HPI ND 110-88W E40 840 120D



General uniform lighting - TForce LED HPI ND 110-88W E40 840 120D


TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data




Light Distribution Diagram - TForce LED HPI ND 110-88W E40 840 120D


Lifetime



Life Expectancy Diagram - TForce LED HPI ND 110-88W E40 840 120D



Lumen Maintenance Diagram - TForce LED HPI ND 110-88W E40 840 120D



Life Expectancy Diagram - TForce LED HPI ND 110-88W E40 840 120D

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

