



A-Shape LED

LED D2D 60W A60 E27 WW FR ND SRT4

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Product data


General Information	
Cap base	E27 [E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	50,000X
Technical type	7.5-60W
Light Technical	
Colour Code	827 [CCT of 2,700 K]
Beam Angle (Nom)	250 °
Luminous flux (nom.)	806 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	107.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 Hz
Power (Rated) (Nom)	7.5 W
Lamp current (nom.)	80 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s

Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	230 V
Temperature	
T-Case maximum (nom.)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Approval and Application	
Energy efficiency label (EEL)	A+
Energy consumption kWh/1,000 hours	8 kWh
Product Data	
Full product code	871869978269600
Order product name	LED D2D 60W A60 E27 WW FR ND SRT4
EAN/UPC – product	8718699782696
Order code	78269600
SAP numerator – quantity per pack	1
SAP numerator – packs per outer box	4

A-Shape LED

Material no. (12 NC)	929001383631
SAP net weight (piece)	0.060 kg



Dimensional drawing



D2D Bulb A19 230V 9.5-60W 2700K E27 ND


Product	D	C
LED D2D 60W A60 E27 WW FR ND SRT4	62 mm	114 mm

Photometric data



LEDbulbD2D 7,5W A19 E27 827 FR

LEDbulbD2D A19 E27 806lm FR



LEDbulbD2D 7,5W A19 E27 827 FR

A-Shape LED

Lifetime



15K LED

15K LMP

