



LED Urban TrueForce Lamps

55ED28/LED/727/ND 120-277V G2 4/1

Philips TrueForce LED high lumen post top lamp makes it easy to upgrade to long lasting, energy saving LED technology without sacrificing your site’s unique outdoor character. Philips TrueForce is a direct replacement option which ensures a perfect fit with existing modern and traditional luminaires. We claim true replacement when comparing flux. This post top lamps can be used in enclosed fixtures.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	727 [CCT of 2700K]
Beam Angle (Nom)	360 degree(s)
Luminous Flux	7,500 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	133.33 lm/W
Color Consistency	ANSI 2700K
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	55 W
Lamp Current (Nom)	460 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	176 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	Others

LED Urban TrueForce Lamps

Approval and Application


Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard

Product Data

Order product name	55ED28/LED/727/ND 120-277V G2 4/1
Full product name	55ED28/LED/727/ND 120-277V G2 4/1
Order code	473652



Material Nr. (12NC)	929001397004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677473655
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677473650

Dimensional drawing




Product	D	C
55ED28/LED/727/ND 120-277V G2 4/1	4-3/16 inch	8-1/16 inch

Photometric data



General uniform lighting - 55ED28/LED/727/ND 120-277V G2 4/1



Light Distribution Diagram - 55ED28/LED/727/ND 120-277V G2 4/1



Spectral Power Distribution Colour - 55ED28/LED/727/ND 120-277V G2 4/1

LED Urban TrueForce Lamps

Lifetime



Life Expectancy Diagram - 55ED28/LED/727/ND 120-277V G2 4/1

Lumen Maintenance Diagram - 55ED28/LED/727/ND 120-277V G2 4/1

