



# T8

## 10T8 LED/48-5000 IF 1PK 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

### Product data

General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Input Frequency	20000-120000 Hz
Nominal lifetime	70,000 hour(s)	Power Consumption	10 W
Switching Cycle	50,000	Lamp Current (Max)	340 mA
Lighting Technology	LED	Lamp Current (Min)	110 mA
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	120-277V; 347 V
Light Technical		Temperature	
Color Code	850 [CCT of 5000K]	Ambient temperature range	-4 °F to 113 °F
Beam Angle (Nom)	180 degree(s)	T-Case Maximum (Nom)	122 °F
Luminous Flux	1,600 lm		
Color Designation	Daylight	Controls and Dimming	
Correlated Color Temperature (Nom)	5000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	160.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	82	Product Length	47-1/4 inch
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	Tube, double-ended
Operating and Electrical			
Line Frequency	20000-120000 Hz		

# T8

## Approval and Application


Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard

## Product Data

Order product name	10T8 LED/48-5000 IF 1PK 10/1
--------------------	------------------------------



Full product name	10T8 LED/48-5000 IF 1PK 10/1
Order code	474007
Material Nr. (12NC)	929001397504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677474003
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677474008

## Dimensional drawing




Product	D1	D2	A1	A2	A3
10T8 LED/48-5000 IF 1PK 10/1	1-1/16 inch	1-1/16 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch

## Photometric data





Spectral Power Distribution Colour - 10T8 LED/48-5000 IF 1PK 10/1

General uniform lighting - 10T8 LED/48-5000 IF 1PK 10/1





Light Distribution Diagram - 10T8 LED/48-5000 IF 1PK 10/1

Lifetime




Life Expectancy Diagram - 10T8 LED/48-5000 IF 1PK 10/1

Life Expectancy Diagram - 10T8 LED/48-5000 IF 1PK 10/1



Life Expectancy Diagram - 10T8 LED/48-5000 IF 1PK 10/1

Lumen Maintenance Diagram - 10T8 LED/48-5000 IF 1PK 10/1



Lumen Maintenance Diagram - 10T8 LED/48-5000 IF 1PK 10/1

