



MasterClass Plastic (WarmGlow) A-Shape Lamps

8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT

Provides a wide variety of premium features, such as best-in-class warm glow dimmability, 25,000 hours long lifetime, and Title 20 certification, ideal for decorative and ambient lighting in high-end retail outlets, hotels, and restaurants.

Product data


General Information		Operating and Electrical	
Cap-Base	E26 [Single Contact Medium Screw]	Line Frequency	60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	60 Hz
Switching Cycle	50,000	Power Consumption	8.8 W
Lighting Technology	LED	Lamp Current (Nom)	80 mA
EU RoHS compliant	Yes	Wattage Equivalent	60 W
Starting Time (Nom)		0.5 s	
Warm-up time to 60% light		0.5 s	
Power Factor (Fraction)		0.7	
Voltage (Nom)		120 V	
Light Technical		Temperature	
Color Code	922-927 [CCT of 2200K-2700K]	T-Case Maximum (Nom)	176 °F
Beam Angle (Nom)	250 degree(s)	Controls and Dimming	
Luminous Flux	800 lm	Dimmable	Yes
Color Designation	Warm White (WW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	2200 2700 K	Bulb Finish	Frosted
Luminous Efficacy (rated) (Nom)	90.00 lm/W		
Color Consistency	<4		
Color rendering index (CRI)	90		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

MasterClass Plastic (WarmGlow) A-Shape Lamps

Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
T20 compliant	Yes
Application Conditions	
can it be used in closed luminaires	Yes



Product Data	
Order product name	8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT
Full product name	8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT
Order code	479444
Material Nr. (12NC)	929001940904
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677479442
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677479447

Dimensional drawing



Product	D	C
8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT	2-1/2 inch	4-7/16 inch

Photometric data




Spectral Power Distribution Colour - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT

General uniform lighting - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT


MasterClass Plastic (WarmGlow) A-Shape Lamps

Photometric data




Light Distribution Diagram - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT

Lifetime



Life Expectancy Diagram - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT



Lumen Maintenance Diagram - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT

