



LED Party Bulbs

8A19/LED/ORANGE/P/ND 120V 6/1BC

Philips A shape party lamps provided a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	10,950 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	10,950 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Beam Angle (Nom)	160 degree(s)
Color Consistency	-
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8 W
Lamp Current (Nom)	115 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	80 °C

Controls and Dimming	
Dimmable	No


Mechanical and Housing	
Bulb Finish	Orange
Bulb Material	Plastic
Bulb Shape	A19 [A 19mm]

Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EyeComfort	Yes

Product Data	
Order product name	8A19/LED/ORANGE/P/ND 120V 6/1BC
Full product name	8A19/LED/ORANGE/P/ND 120V 6/1BC
Order code	929001998203
Material Nr. (12NC)	929001998203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463236
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677463231



LED Party Bulbs

Dimensional drawing




Product	D	C
8A19/LED/ORANGE/P/ND 120V 6/1BC	60 mm	107 mm

Photometric data



Light Distribution Diagram



Spectral Power Distribution Colour - 8A19/LED/ORANGE/P/ND 120V 6/1BC



General uniform lighting - 8A19/LED/ORANGE/P/ND 120V 6/1BC

LED Party Bulbs

Lifetime



Lumen Maintenance Diagram - 8A19/LED/ORANGE/P/ND 120V 6/1BC

Life Expectancy Diagram - 8A19/LED/ORANGE/P/ND 120V 6/1BC

