



CorePro Plastic (Dimmable) A-Shape Lamps

8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Product data

General Information		Input Frequency	
Cap-Base	E26 [Single Contact Medium Screw]	Input Frequency	60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	8.8 W
Switching Cycle	50,000	Lamp Current (Nom)	80 mA
Lighting Technology	LED	Wattage Equivalent	60 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	927	T-Case Maximum (Nom)	90 °C
Beam Angle (Nom)	250 degree(s)		
Luminous Flux	800 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Correlated Color Temperature (Nom)	2700 K		
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Mechanical and Housing	
Color Consistency	<4	Bulb Finish	Frosted
Color rendering index (CRI)	90	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A19
Operating and Electrical			
Line Frequency	60 Hz		

CorePro Plastic (Dimmable) A-Shape Lamps

UL Wet/ damp/ dry location	Damp location
----------------------------	---------------

Approval and Application

Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
T20 compliant	Yes

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data

Order product name	8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT
--------------------	---------------------------------------



Full product name	8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT
Order code	929002036104
Material Nr. (12NC)	929002036104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677550431
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677550436

Dimensional drawing



Product	D	C
8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm

Photometric data




General uniform lighting - 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT

Spectral Power Distribution Colour - 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT

CorePro Plastic (Dimmable) A-Shape Lamps

Photometric data



Light Distribution Diagram - 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT

Lifetime



Life Expectancy Diagram - 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT



Lumen Maintenance Diagram - 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT

