



# LED PAR38

## 14PAR38/COR/930/F25/DIM/120V T20 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

### Product data


General Information		Wattage Equivalent	
Cap-Base	E26 [Single Contact Medium Screw]		120 W
Nominal lifetime	25,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	930 [CCT of 3000K]	T-Case Maximum (Nom)	85 °C
Beam Angle (Nom)	25 degree(s)	Controls and Dimming	
Luminous Flux	1,300 lm	Dimmable	Yes
Luminous Intensity (Nom)	5,382 cd	Mechanical and Housing	
Color Designation	White (WH)	Bulb Finish	Clear
Correlated Color Temperature (Nom)	3000 K	Bulb Material	Plastic
Luminous Efficacy (rated) (Nom)	92.00 lm/W	Bulb Shape	PAR38
Color Consistency	<4	Approval and Application	
Color rendering index (CRI)	90	Suitable For Accent Lighting	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	- kWh
Operating and Electrical		Energy Certifications	Energy Star
Line Frequency	50 to 60 Hz	Product Data	
Input Frequency	50 to 60 Hz	Order product name	14PAR38/COR/930/F25/DIM/120V T20 6/1FB
Power Consumption	14 W		
Lamp Current (Nom)	136 mA		

# LED PAR38

Full product name	14PAR38/COR/930/F25/DIM/120V T20 6/1FB
Order code	929002045204
Material Nr. (12NC)	929002045204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677546946


Numerator - Packs per outer box	6
EAN/UPC - Case	50046677546941

## Dimensional drawing




Product	D	C
14PAR38/COR/930/F25/DIM/120V T20 6/1FB	125 mm	131 mm

## Photometric data




© 2024 Philips Lighting B.V. All rights reserved.



Accent Lighting Spots - 14PAR38/COR/930/F25/DIM/120V T20 6/1FB

Light Distribution Diagram - 14PAR38/COR/930/F25/DIM/120V T20 6/1FB



Spectral Power Distribution Colour - 14PAR38/COR/930/F25/DIM/120V T20 6/1FB

# LED PAR38

## Lifetime



Life Expectancy Diagram - 14PAR38/COR/930/F25/DIM/120V T20 6/1FB

Lumen Maintenance Diagram - 14PAR38/COR/930/F25/DIM/120V T20 6/1FB

