



# LED Small Spots

## 4GU10/LED/927-22/F35/G/WG/T20 10/1

Philips standard and Glass LED spots are a perfect fit for basic spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 socket and are designed as a retrofit replacement for halogen spots. They provide the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data

General Information	
Cap-Base	GU10 [GU10]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Beam Angle (Nom)	35 degree(s)
Luminous Flux	380 lm
Luminous Intensity (Nom)	600 cd
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	95.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	4 W
Lamp Current (Nom)	50 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	149 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	MR16
UL Wet/ damp/ dry location	Damp location
Approval and Application	
Suitable For Accent Lighting	Yes

## LED Small Spots

Energy Consumption kWh/1000 h	- kWh
T20 compliant	Yes

### Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

### Product Data

Order product name	4GU10/LED/927-22/F35/G/WG/T20 10/1
Full product name	4GU10/LED/927-22/F35/G/WG/T20 10/1



Order code	471565
Material Nr. (12NC)	929002055304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677471569
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677471564

## Dimensional drawing



Product	D	C
4GU10/LED/927-22/F35/G/WG/T20 10/1	2 inch	2-1/8 inch

## Photometric data




Light Distribution Diagram - 4GU10/LED/927-22/F35/G/WG/T20 10/1

Accent Lighting Spots - 4GU10/LED/927-22/F35/G/WG/T20 10/1


# LED Small Spots

## Photometric data




Spectral Power Distribution Colour - 4GU10/LED/927-22/F35/G/WG/T20 10/1

## Lifetime



Lumen Maintenance Diagram - 4GU10/LED/927-22/F35/G/WG/T20 10/1



Life Expectancy Diagram - 4GU10/LED/927-22/F35/G/WG/T20 10/1

