



A-Shape LED

16.6A21/LED/950/P/E26/ND 6/1FB T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data


General Information		Wattage Equivalent	
Cap-Base	E26 [Single Contact Medium Screw]	100 W	
Nominal lifetime	11,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	11,000 hour(s)	Power Factor (Fraction)	0.7
Lighting Technology	LED	Voltage (Nom)	120 V
EU RoHS compliant	Yes	Temperature	
Light Technical		T-Case Maximum (Nom)	100 °C
Color Code	950 [CCT of 5000K]	Controls and Dimming	
Beam Angle (Nom)	210 degree(s)	Dimmable	No
Luminous Flux	1,500 lm	Mechanical and Housing	
Color Designation	Daylight	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	5000 K	Bulb Material	Plastic
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Bulb Shape	A21 [A 21mm]
Color Consistency	<4	Approval and Application	
Color rendering index (CRI)	90	Energy Consumption kWh/1000 h	- kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %	EyeComfort	Yes
Operating and Electrical		Product Data	
Line Frequency	60 Hz	Order product name	16.6A21/LED/950/P/E26/ND 6/1FB T20
Input Frequency	60 Hz	Full product name	16.6A21/LED/950/P/E26/ND 6/1FB T20
Power Consumption	16.6 W		
Lamp Current (Nom)	145 mA		

A-Shape LED

Order code	929002227704
Material Nr. (12NC)	929002227704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677554484



Numerator - Packs per outer box	6
EAN/UPC - Case	50046677554489

Dimensional drawing




Product	D	C
16.6A21/LED/950/P/E26/ND 6/1FB T20	78 mm	140 mm

Photometric data



General uniform lighting - 16.6A21/LED/950/P/E26/ND 6/1FB T20


Spectral Power Distribution Colour - 16.6A21/LED/950/P/E26/ND 6/1FB T20



Light Distribution Diagram - 16.6A21/LED/950/P/E26/ND 6/1FB T20

A-Shape LED

Lifetime



Life Expectancy Diagram - 16.6A21/LED/950/P/E26/ND 6/1FB T20

Lumen Maintenance Diagram - 16.6A21/LED/950/P/E26/ND 6/1FB T20

