



# LED AR111

## 12AR111/LED/930/S8/DIM/EC 12V 6/1FB

With an elegant new design, Philips MasterClass LED AR111 creates a brilliant visual effect. With excellent rendering of 90+ CRI and R9>50, colors stay vibrant and natural, enhancing the appeal of everything on display.

### Product data

General Information	
Cap-Base	G53
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	8 degree(s)
Luminous Flux	680 lm
Luminous Intensity (Nom)	8,000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	56.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	12 W
Lamp Current (Nom)	1,300 mA

Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	AR111
UL Wet/ damp/ dry location	Damp location
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	No
T20 compliant	N/A

# LED AR111

## Application Conditions

can it be used in closed luminaires No

## Product Data

Order product name	12AR111/LED/930/S8/DIM/EC 12V 6/1FB
Full product name	12AR111/LED/930/S8/DIM/EC 12V 6/1FB
Order code	929002238504

Material Nr. (12NC) 929002238504


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 046677552404

Numerator - Packs per outer box 6



EAN/UPC - Case 50046677552409

## Dimensional drawing



Product	D	C
12AR111/LED/930/S8/DIM/EC 12V 6/1FB	111 mm	62 mm


## Photometric data



Copyright: Photometric Ltd. All rights reserved. Page 1/1

Spectral Power Distribution Colour - 12AR111/LED/930/S8/DIM/EC 12V 6/1FB



General uniform lighting - 12AR111/LED/930/S8/DIM/EC 12V 6/1FB



Light Distribution Diagram - 12AR111/LED/930/S8/DIM/EC 12V 6/1FB

# LED AR111

## Lifetime



Life Expectancy Diagram - 12AR111/LED/930/S8/DIM/EC 12V 6/1FB

Lumen Maintenance Diagram - 12AR111/LED/930/S8/DIM/EC 12V 6/1FB

