



Classic filament LEDbulbs

LED classic 150W A67 E27 WW FR NDRFSRT4

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Colour Code	827 [CCT of 2700K]
Colour Code	827 [CCT of 2700K]
Luminous Flux	2,452 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	140.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1

Stroboscopic effect	0.4
Photobiological safety according to EN 62471	RGO
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	17.5 W
Lamp current (nom.)	150 mA
Wattage equivalent	150 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	60 °C
Controls and Dimming	
Dimmable	No

Classic filament LEDbulbs

Mechanical and Housing

Lamp Finish	Frosted
Bulb shape	A67 [A 67 mm]

Approval and Application


Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	18 kWh
EPREL registration number	374905
EyeComfort	Yes

Product Data

Order product name	LED classic 150W A67 E27 WW FR NDRFSRT4
--------------------	--


Full product name	LED classic 150W A67 E27 WW FR NDRFSRT4
Full EOC	871869976457900
Order code	76457900
Material no. (12 NC)	929002372601
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699764579
Numerator – packs per outer box	4
EAN/UPC – Case	8718699764586

Dimensional drawing




Product	D	C
LED classic 150W A67 E27 WW FR NDRFSRT4	70 mm	121 mm

Photometric data




Spectral Power Distribution Colour - LED classic 150W A67 E27 WW FR NDRFSRT4



Light Distribution Diagram - LED classic 150W A67 E27 WW FR NDRFSRT4

Classic filament LEDbulbs

Photometric data




General uniform lighting - LED classic 150W A67 E27 WW FR NDRFSRT4

Lifetime



Life Expectancy Diagram - LED classic 150W A67 E27 WW FR NDRFSRT4



Lumen Maintenance Diagram - LED classic 150W A67 E27 WW FR NDRFSRT4

