



GENIE

GENIE 14W WW E27 220-240V 1PF/6

Functional non-covered Energy saving lamp, with money saving high quality light and compact design. This lamp is small enough to fit neatly wherever you need extra bright light at home, enables easy replacement of most incandescent lamp all the way.

Advertencias y seguridad

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Datos del producto

Información general	
Base del casquillo	E27 [E27]
Vida útil nominal	10.000 hora(s)
Ciclo de encendido/apagado	10.000
Vida útil nominal (horas)	10.000 hora(s)
Lighting Technology	Compact Fluorescent Integrated
Datos técnicos de la luz	
Código de color	827 [CCT of 2700K]
Flujo luminoso	810 lm
Designación de color	Blanco cálido (WW)
Coordenada X de cromacidad (Nom)	463
Coordenada Y de cromacidad (Nom)	420
Temperatura de color correlacionada (Nom)	2700 K
Eficacia lumínica (nominal) (nom.)	58 lm/W
Índice de reproducción cromática (IRC)	80

LLMF al fin de vida útil nominal (nom.)	65 %
Operativos y eléctricos	
Line Frequency	50 or 60 Hz
Frecuencia de entrada	50 o 60 Hz
Consumo de energía	14 W
Corriente de lámpara (nom.)	100 mA
Hora de inicio (nom.)	0,3 s
Factor de potencia (fracción)	0.6
Voltaje (nom.)	220-240 V
Controles y regulación	
Regulable	No

Mecánicos y de carcasa

Forma de la bombilla	Barra
----------------------	-------

Aprobación y aplicación


Contenido de mercurio (Hg) (máx.)	2 mg
Contenido de mercurio (Hg) (nom.)	1,5 mg
Consumo energético kWh/1000 h	14 kWh

Datos de producto

Nombre de producto del pedido	GENIE 14W WW E27 220-240V 1PF/6
-------------------------------	---------------------------------

Nombre completo del producto	GENIE 14W WW E27 220-240V 1PF/6
Full EOC	871150080120310
Código de pedido	80120310
Código 12NC	929689243501
Cantidad por paquete	1
EAN/UPC - Producto/Caja	8711500801203
Numerador SAP - Paquetes por caja exterior	6
Embalaje con código EAN/UPC	8711500801708

Plano de dimensiones



Product	D (max)	C (max)	F (max)
GENIE 14W WW E27 220-240V 1PF/6	35,0 mm	127 mm	44,5 mm

