



# GENIE

## GENIE 14W CDL E27 220-240V 1PF/6

Functional non-covered Energy saving lamp, with money saving high quality light and compact design. This lamp is small enough to fit neatly wherever you need extra bright light at home, enables easy replacement of most incandescent lamp all the way.

### Advertencias y seguridad

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Datos del producto

Información general		LLMF al fin de vida útil nominal (nom.)	
Base del casquillo	E27 [E27]		65 %
Vida útil nominal	10.000 hora(s)	Operativos y eléctricos	
Ciclo de encendido/apagado	10.000	Line Frequency	50 or 60 Hz
Vida útil nominal (horas)	10.000 hora(s)	Frecuencia de entrada	50 o 60 Hz
Lighting Technology	Compact Fluorescent Integrated	Consumo de energía	14 W
Datos técnicos de la luz		Corriente de lámpara (nom.)	100 mA
Código de color	865 [CCT of 6500K]	Hora de inicio (nom.)	0,3 s
Flujo luminoso	760 lm	Factor de potencia (fracción)	0.6
Designación de color	Luz natural fría	Voltaje (nom.)	220-240 V
Coordenada X de cromacidad (Nom)	313	Controles y regulación	
Coordenada Y de cromacidad (Nom)	337	Regulable	No
Temperatura de color correlacionada (Nom)	6500 K		
Eficacia lumínica (nominal) (nom.)	54 lm/W		
Índice de reproducción cromática (IRC)	80		

# GENIE

## Mecánicos y de carcasa

Forma de la bombilla	Barra
----------------------	-------

## Aprobación y aplicación


Contenido de mercurio (Hg) (máx.)	2 mg
Contenido de mercurio (Hg) (nom.)	1,5 mg
Consumo energético kWh/1000 h	14 kWh

## Datos de producto

Nombre de producto del pedido	GENIE 14W CDL E27 220-240V 1PF/6
-------------------------------	----------------------------------

Nombre completo del producto	GENIE 14W CDL E27 220-240V 1PF/6
Full EOC	871150080107410
Código de pedido	80107410
Código 12NC	929689243601
Cantidad por paquete	1
EAN/UPC - Producto/Caja	8711500801074
Numerador SAP - Paquetes por caja exterior	6
Embalaje con código EAN/UPC	8711500801579

## Plano de dimensiones



Product	D (max)	C (max)	F (max)
GENIE 14W CDL E27 220-240V 1PF/6	35,0 mm	127 mm	44,5 mm

