DESCRIPTION

Super-Adjustable is a downlight with pull-down action that allows up to 80° tilt. The trim features die-cast aluminum construction for high-quality fit and finish. The 3010 Super-Adjustable uses MR16 low voltage or GU10 line voltage lamps in Halo H3 line and low voltage housings. The 3010 trim is available in multiple finishes to match interior decor. The 3010 Super-Adjustable is ideal for accent and task lighting. Super Adjustable trim offers 360° orientation within housing.

Catalog #	Туре
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

Super-Adjustable trim is available in Matte White, Satin Nickel, or Tuscan Bronze finishes. Nylon ball bearings and silicone guides retain adjustable and ensure smooth movement with firm positioning. Lamp replacement is via twist-lock front loading baffle-collar. Three pressure springs ensure positive retention in housing.

Trim includes cover glass lens which may be replaced with a variety of media. (Lamps that have integral glass lens do not require use of the cover glass supplied with this trim.)

3010 is designed for use with the following Halo H3 small aperture housings:

• Line Voltage Housing (for 120V GU10 lamps).

H36ICAT 50W IC Air-Tite Housing H36TAT 50W Non-IC Air-Tite Housing

H36RTAT 50W Non-IC Air-Tite Remodel Housing

• Low Voltage Housing (for 12V MR16 lamps).

H36LVICAT 50W IC Air-Tite Housing H36LVTAT 50W Non-IC Air-Tite Housing

H36LVRTAT 50W Non-IC Air-Tite Remodel Housing H36LVTAT277 50W Non-IC Air-Tite Housing, 120/277V

H36LVRTAT277 50W Non-IC Air-Tite Remodel Housing, 120/277V


• Line Voltage Housing (for 120V GU10 lamps).

H38ICAT 50W IC Air-Tite Housing

• Low Voltage Housing (for 12V MR16 lamps).

H38LVICAT 50W IC Air-Tite Housing





Baffle Aperture: 1-3/4" [45mm]
Adjustable Tube Diameter: 2-3/8" [60mm]
Baffle-Collar Outside Diameter: 2-1/2" [64mm]
Ceiling Opening: 3-3/4" [95mm]
Outside Diameter: 4-1/4" [108mm]

ORDERING INFORMATION

SAMPLE NUMBER: 3010WH

Order housing and trims separately.

Trim	1	Finish
3010	= 3" Super-AdjustableTrim, 0-80°Tilt	WH=White SN=Satin Nickel TBZ=Tuscan Bronze



3010WH White Super-Adjustable



3010SN Satin Nickel Super-Adjustable



3010TBZ Tuscan Bronze Super-Adjustable

3010

3" Super-Adjustable

3" TRIM