

DESCRIPTION

The 147 series is a decorative pendant family with a square cylindrical form. This product has a tall square cylindrical shade with a variety of options. The integral LED light engine is available in 2700K, 3000K, 3500K, 4000K color temperatures that evenly illuminates the shades and bottom lens with 83+ CRI. The stem, canopy, and finial finishes are available in many painted options. Shaper's Fabrique collection is known for its high quality hand tucked fabrics. Shades come in 2 standard sizes, 11 standard fabrics, 3 vinyl materials, and 4 printed woods patterns as well as the option to add 1 of 2 translucent organza outer shade fabrics. This series also comes with the option for a 3 or 4 pendant cluster.

SPECIFICATION FEATURES

Materials

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Matte white acrylic bottom diffuser with one finial, standard. Optional matte white acrylic top cover available (TC).

5" diameter canopy with self aligning swivel. Stem is 1/2" aluminum tubing with threaded rod. Air craft cable option is 3/64" cable. Slope adapter option available (SCA-XX - 18°- 45°, but slope dimension must be provided).

28" H x 10" L x 10" W

Standard Length=

40" OAH (Overall Height)

Min	Max
32" OAH	96" OAH

40" H x 10" L x 10" W

Standard Length=

54" OAH (Overall Height)

Min	Max
44" OAH	96" OAH

Stem Options

Single Rigid Stem	-P1S
Air Craft Cable	-P1SAC
3 Stem Cluster	-3FCL
4 Stem Cluster	-4FCL

Consult factory for non standard lengths under 18" and over 96".

Painted Finishes

ALP (Aluminum Paint)
 BM (Bronze Metallic)
 DP (Dark Platinum)
 GRM (Graphite Metallic)
 MB (Matte Black)
 MW (Matte White)
 CC (Custom Color - Specify)
 For Custom Color contact factory for quotation.

Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl. Shade in Shade offers 2 material selections, overlapping each other.

Fabric Shade Selections

SIW - Silk White
 SIY - Silk Ivory
 SWH - Shantung White
 SEG - Shantung Eggshell
 SBG - Shantung Beige
 LAT - Linen Alabaster
 LCK - Linen Chopstick
 NGS - Silk Glow
 GBB - Glynn Brussels Beige
 LOLA - Lola Sand
 VLW - Verona Linen White

Vinyl Coated Fabric

ABR - Alabaster Vinyl
 NFX - Natural Flax
 GHY - Golden Honey

Printed Wood

PVDB - Varigated Bamboo
 PMA - Maple
 PCH - Cherry
 PWA - Walnut

Note: For humid environments, such as showers or open

Catalog #		Type
Project		
Comments		Date
Prepared by		

lobbies, Vinyl Coated Fabrics are recommended.

LEDs

LEDs are offered in four color temperatures: 2700K, 3000K, 3500K, and 4000K CCTs at 80+ CRI. Rated Rated LED Life: 50,000 hrs.

Electrical

Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

Control

Standard driver is 0-10V with 10% dimming.

Compliance

Components are UL recognized and luminaires are cUL listed for 25" environments. Fixtures are rated for damp location listing. Made in North America. All LED components are RoHS compliant and drivers conform to appropriate FCC regulations. Sconce products meet ADA regulations.

Certifications

All Fabrique Collection products are UL and cUL approved for interior damp locations. All LED components in the Fabrique Collection are RoHS compliant and drivers conform to appropriate FCC regulations.

Life and Warranty

Standard five-year warranty on all parts.



147 SERIES

Height: 28"

- Delivered Lumens (@3500K): 1959
- Wattage: 19W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

Diameter: 40"

- Delivered Lumens (@3500K): 2790
- Wattage: 28W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

ORDERING INFORMATION (SELECT FIXTURE AND FABRIC KIT TO COMPLETE SPECIFICATION)

Fixture Number: 147-28-P1S-L3/827-UNV-ALP-40

Shade Number: 147-28-SHD-SWH

Series ¹	Shade Height	Mounting Type	Lamp	LED Voltage	Finish	Options ²	Overall Height (OAH)
147 = Square Cylinder Pendant ¹	28 = 28" 40 = 40"	P1S = Single Stem P1SAC = Single Stem with Aircraft Cable 3FCL = 3 Stem Cluster 4FCL = 4 Stem Cluster	28" L3/827 L3/830 L3/835 L3/840 40" L4/827 L4/830 L4/835 L4/840	UNV (120-277)	MW = Matte White MB = Matte Black BM = Bronze Metallic DP = Dark Platinum ALP = Aluminum Paint GRM = Graphite Metallic CC = Custom Color specify	SCA = Sloped ceiling adapter 18'-45" TC = Matte White Acrylic Top Cover	40 = 40" OAH (28" shade height) 54 = 54" OAH (40" shade height) XX = Custom length must be specified (147-28 = 32" - 96" 147-40 = 44" - 96") See "Dimensions" section for Overall Height per fixture length per cluster type.

Notes: ¹ Fabric shade not included. Please specify fabric shade from selections provided to complete fixture order. ² Sloped ceiling adapter can accommodate up to 18-45 degree slope. Slope dimension must be provided. ³ Shade in Shade option for Fabric selections only.


ORDERING INFORMATION (SELECT FIXTURE AND FABRIC KIT TO COMPLETE SPECIFICATION)

Shade Number: 147-28-SHD-SWH

Series	Size	SHD	Finish			Options
147 = Rectangular Cylinder Shade	28 = 28" 40 = 40"	SHD = Shade	Fabric: SIW = Silk White SIY = Silk Ivory SWH = Shantung White SEG = Shantung Eggshell SBG = Shantung Beige LAT = Linen Alabaster LCK = Linen Chopstick	NGS = Silk Glow GBB = Glynn Brussels Beige LOLA = Lola Sand	Printed Wood: PVDB = Varigated Bamboo PMA = Maple PCH = Cherry PWA = Walnut Vinyl Coated Fabric: ABR = Alabaster Vinyl NFX = Natural Flax GHY = Golden Honey	Organza Outer Shade TSQISIS-EDT = Top Square-in Shade, Earth Dust TSQISIS-WMT = Top Square-in Shade, White Mist

OPTIONS


MOUNTING TYPES - SINGLE PENDANT




147-P-TC
(TOP COVER)




147-P-SCA
(SLOPED CEILING ADAPTOR)



147-28-P1S
(SINGLE STEM)




147-40-P1S
(SINGLE STEM)




147-P
(PLAN VIEW)


MOUNTING - SINGLE PENDANT - SHADE IN SHADE



147-28-P1S-TSQISIS
(TOP SQUARE SHADE-IN-SHADE)






147-40-P1S-TSQISIS
(TOP SQUARE SHADE-IN-SHADE)



147-P-TSQISIS
(PLAN VIEW)

DIMENSIONS - 3 CLUSTER PENDANT



DIMENSIONS - 4 CLUSTER PENDANT

