PHILIPS

4404.016.98661 Last update: 23/10/14











- 01- The product should only be installed indoors.
- 01- 产品只能安装在室内。
- 02- The product is not suitable for installation in bathrooms, certainly not in the specified zone.
- 02-产品不可安装在浴室中,尤其不能在指定区域内。
- 03- The product is suitable for mounting on normally flammable surfaces.
- 03-产品可安装在普通易燃表面。
- 04- The product is suitable for mounting on the wall or on the ceiling.
- 04-产品可安装在墙上或天花板上。
- 05- Protection class III: the product or component is only suitable for safety extra low voltage supply (<50Va.c.; <120Vd.c.).
- 05- 防护等级 Ⅲ: 产品或组件仅用于安全超低供电电压(交流〈50伏、直流〈120伏)。

LED strip do not connect with LED driver during transportation.

灯带在包装盒里不得接通电源。

LED strip can not be electrical connection with unspecified Philips light strip.

本灯带不得与非指定飞利浦灯带电气连接。

LEDs are un-replaceable, only allow to replace identical Philips LED strip. 灯珠不可更换。

Driver is excluded. Recommend Philips driver: 913710052466

Driver type: Uout 12V DC Constant Voltage. LED strip power consume: 3.6W/m.

本产品不含电源驱动器,推荐使用飞利浦品牌驱动器:913710052466 适用规格:12V直流恒压输出电源驱动器。灯带消耗功率:3.6瓦/米。

Decorative LED strip 装饰性LED灯带

PHILIPS

