

# Shaper

## DESCRIPTION

The 142 series is a decorative pendant family with a circular form. This product is a drum shape shade, with a variety of options to highlight elegant spatial forms. The integral LED light engine is available in 2700K, 3000K, 3500K, and 4000K color temperatures that evenly illuminates the shade and the bottom lens, with 83+ CRI. The stem, canopy, and finial finishes are available in many painted options. Shaper's Fabrique collection is known for its high quality hand tucked fabrics. Heavy gauged steel frame, laminated styrene backing, and minimum internal structure. Shades come in four standard sizes, eleven standard fabrics, three vinyl materials, and four printed wood patterns.

## SPECIFICATION FEATURES

### Material/Mounting

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Matte white acrylic bottom diffuser with one finial, standard. Optional matte white acrylic top cover available (TC).

5" diameter canopy with self aligning swivel. Stem is 1/2" aluminum tubing with threaded rod. Air craft cable option is 3/64" cable. Slope adapter option available (SCA-XX - 18°- 45°, but slope dimension must be provided).

### 24" Diameter

Standard length = 24" OAH (Overall Height)

Min	Max
12" OAH	96" OAH

### 30" Diameter

Standard length = 28" OAH (Overall Height)

Min	Max
14" OAH	96" OAH

### 36" Diameter

Standard length = 34" OAH (Overall Height)

Min	Max
16" OAH	96" OAH

### 42" Diameter

Standard length = 40" OAH (Overall Height)

Min	Max
18" OAH	96" OAH

Stem Options	
Single Rigid Stem	-P1S
Single Stem Air Craft Cable	-P1SAC

Consult factory for non standard lengths under min and over 96".

### Painted Finishes

(canopy, stem, and finial)  
ALP (Aluminum Paint)  
BM (Bronze Metallic)  
DP (Dark Platinum)  
GRM (Graphite Metallic)  
MB (Matte Black)  
MW (Matte White)  
CC (Custom Color - Specify)  
Consult factory for custom color.

### Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl.

### Fabric Shade Selections

SIW - Silk White  
SIY - Silk Ivory  
SWH - Shantung White  
SEG - Shantung Eggshell  
SBG - Shantung Beige  
GBB - Glynn Brussels Beige  
LOLA - Lola Sand  
NGS - Silk Glow  
LCK - Linen Chopstick  
LAT - Linen Alabaster  
VLW - Verona Linen White

### Vinyl Coated Fabric

ABR - Alabaster Vinyl  
NFX - Natural Flax  
GHY - Golden Honey

**Note:** For humid environments, such as showers or open lobbies, Vinyl Coated Fabrics are recommended.

### Printed Woods

PVDB - Varigated Bamboo  
PMA - Maple  
PCH - Cherry  
PWA - Walnut

### LEDs

LEDs are offered in four color temperatures: 2700K, 3000K, 3500K, and 4000K CCTs at 80+ CRI. Rated Lamp Life: 50,000 hrs

### Electrical

Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

### Control

Standard driver is 0-10V with 10% dimming.

### Compliance

Components are UL recognized and luminaires are cUL listed for 25° ambient environments. Fixtures are rated for damp location listing. All LED components are RoHS compliant and drivers conform to appropriate FCC regulations. Sconce products meet ADA regulations.

### Life and Warranty

Standard five-year warranty on all parts.



## 142 SERIES

### Diameter: 24"

- Delivered Lumens (@3500K): 4404
- Wattage: 47W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K

### Diameter: 30"

- Delivered Lumens (@3500K): 4347
- Wattage: 47W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K

### Diameter: 36"

- Delivered Lumens (@3500K): 6981
- Wattage: 82W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K

### Diameter: 42"

- Delivered Lumens (@3500K): 10,050
- Wattage: 105W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K



Light ARchitect™

## ORDERING INFORMATION (Select FIXTURE NUMBER and SHADE NUMBER to complete specification)

Fixture Number: 142-30-P1S-L5/827-UNV-MW-TC-28

Series <sup>1</sup>	Size	Mounting Type	LED Lamp		LED Voltage	Finish	Options <sup>2</sup>	Overall Height (OAH)
			24"	30"				
142 = Drum Pendant	24 = 24" 30 = 30" 36 = 36" 42 = 42"	P1S = Single Stem P1SAC = Single Stem with Aircraft Cable	L5/827	L5/827	UNV (120-277)	MW = Matte White MB = Matte Black BM = Bronze Metallic DP = Dark Platinum ALP = Aluminum Paint GRM = Graphite Metallic CC = Custom Color specify	SCA = Sloped ceiling adapter 8'-45' TC = Matte White Acrylic Top Cover	24 = 24" OAH 28 = 28" OAH 34 = 34" OAH 40 = 40" OAH XX = custom length must be specified (142-24=12"- 96") (142-30=14"- 96") (142-36=16"- 96") (142-42=18"- 96")
			L5/830	L5/830				
			L5/835	L5/835				
			L5/840	L5/840				
			36"	42"				
			L9/827	L12/827				
			L9/830	L12/830				
			L9/835	L12/835				
			L9/840	L12/840				

Notes: <sup>1</sup> Fabric shade not included. Please specify fabric shade from selections provided to complete fixture order. <sup>2</sup> Sloped ceiling adapter can accommodate up to 8-45 degree slope. Slope dimension must be provided.


<sup>3</sup> Shade in Shade option for Fabric selections only.

**ORDERING INFORMATION (Select FIXTURE NUMBER and SHADE NUMBER to complete specification)**


Shade Number: 142-30-SHD-SIW

Series	Size	SHD	Finish		
142 = Drum Shade	24 = 24" 30 = 30" 36 = 36" 42 = 42"	SHD = Shade Fabric	<b>Fabric:</b> SIW = Silk White SIY = Silk Ivory SWH = Shantung White SEG = Shantung Eggshell SBG = Shantung Beige GBB = Glynn Brussels Beige	LOLA = Lola Sand NGS = Silk Glow LCK = Linen Chopstick LAT = Linen Alabaster VLW = Verona Linen White	<b>Vinyl:</b> ABR = Alabaster Vinyl NFX = Natural Flax GHY = Golden Honey


**DIMENSIONS (SINGLE STEM: P1S)**




**SINGLE STEM WITH DECORATIVE AIR CRAFT CABLE: P1SAC**



**OPTIONS**



**TOP COVER (TC)**



**SLOPED CEILING ADAPTOR (SCA)**