


Project		Catalog #		Type	
Prepared by		Notes		Date	



Metalux

APSHP

3' and 4' LED Utility Shoplight

Typical Applications

Work Benches • Counters • Work Shops • Studios • Storage Areas • General Task Lighting

Interactive Menu

- Order Information [page 2](#)
- Photometric Data [page 2](#)
- Product Warranty

Product Certification







Product Features



Top Product Features

- 105 lm/W efficacy and up to 4000 lumen output
- Ideal for replacing single or two lamp fluorescent fixtures
- Integrated reflector design focuses light where you need it
- 5ft 120V grounded plug-in power cord
- Easy on/off convenience with included pull chain (4APSHP only)

Dimensional and Mounting Details



Order Information

Catalog	UPC	CCT (K)	CRI (Min)	Delivered lumens	Watts (W)	Efficacy (lm/W)	Controls	Input current (A)	
								120V	277V
3APSHP3040R	080083834570	4000	80	3200	30	108	Non-Dimming	0.25	
4APSHP4040R	080083834594	4000	80	4300	40	108	Non-Dimming	0.33	

Product Specifications

Construction

- Rigid, light weight extruded housing
- Molded white endcaps joins LED and driver into single assembly
- Extruded lens and reflector optic
- Anodized housing exterior and white reflector finish
- Available sizes: 3' and 4' nominal lengths

Electrical

- 120V, FCC rated Class B, non-dimming driver
- 5ft grounded cord & plug included
- On-off pull chain for easy operation (4APSHP model only)
- L70 at 50,000 rated life-hours (TM-21), or greater than 43 years at 3 hrs/day
- LEDs are 4000K CCT and 80 CRI minimum

Shielding

- UV-stabilized lens
- Integrated reflector design focuses light where you need it
- See acrylic cleaning and limitations on use

Installation

- Suspension mount using included 10 inch chain and S-hook
- Plug and play installation using 5ft cord & plug

Compliance


- UL/cUL listed for dry location
- ENERGY STAR® Certified luminaire - consult ENERGY STAR® Certified Product List
- Low-start temperature rated at 0F (-20C)
- RoHS compliant
- LED complies with IESNA LM-79 and LM-80

Warranty


- Five year warranty.

Photometric Data

[View IES files](#)



4APSHP4040R
 Electronic Driver
 Linear LED 4000K
 Spacing criterion: (||) 1.2 x mounting height,
 (⊥) 1.3 x mounting height
 Lumens: 4389
 Input Watts: 39.8W
 Efficacy: 110 lm/W
 Test Report: 4APSHP4040R.IES



3APSHP3040R
 Electronic Driver
 Linear LED 4000K
 Spacing criterion: (||) 1.2 x mounting height,
 (⊥) 1.3 x mounting height
 Lumens: 3252
 Input Watts: 29.6W
 Efficacy: 110 lm/W
 Test Report: 3APSHP3040R.IES

Features and Benefits

	Feature	Benefit	Result
Performance	Uniform illumination	Safe work area	Peace of mind
	50 K rated life-hours	Long life	Save money
	5-year warranty	Guaranteed quality	Peace of mind
Construction	Long life LED source	No costly lamp replacements	Save money
	5 foot cord & plug with on/off pull chain	Easy to transport from project to project	Save time
	Extruded aluminum housing	Rugged long life fixture	Peace of mind

Load Data

	3'	4'
PF	8.6	9.9
THD%	.99	.99
Weight	1.3	1.8
Low Temp. Start	-20°C	-20°C

Shipping Data

Catalog Base	Wt.	Units per Pallet	Gross wt. Pallet
3APSHP	2.2	192	514
4APSHP	2.6	144	513