

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Reflector Trims — See Individual Reflector Trim Specification Sheets												
	Open Downlight						Recessed Adjustable	Enclosed Diffusers	Wall Washer	Open Wet Location			
Reflector	Cone	Satin Cone	Baffles	Basic White	Pinhole								
1003R	1045	1012	1008	1005	1071	1011	1027	1038	1021	1035	1084CD		
	1046	1012NM	1008NM	1005WH			1027WH	1038NM	1024	1035WH	1084WH		
	1046CD	1013	1010	1005NM				1027BK	1048	1078	1085		
			1010NM	1005BNM				1027NM	1048NM	1090			
			1076					1027BNM					
			1076WH					1027CD					
								1027BKNM					
								1027CDNM					
			Eyeball:										
									1022				
						1022WH							
						1082							

1003R Lytecaster INC 5"

Non-IC Remodeler

Features

- 1. Mounting Ring:** .032 (#22 ga.) galvanized steel. Accommodates existing ceilings up to 2" thick. Attaches securely to any type of ceiling material without tools using (3) mounting straps provided. Push-in/twist-out clips hold reflector flush to ceiling. Includes adhesive backed aperture template.
- 2. Junction Box:** 2 1/2" X 2 1/2" X 3 1/2" (21 cu. in.) .032 (#22 ga.) galvanized steel. U.L. listed for 90° C supply wire. Integral cable clamps permit attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors. Attaches to mounting ring without tools.
- 3. Socket Housing:** Impact extruded aluminum or galvanized steel.
- 4. Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 VOLT 200° C) leads to junction box.
- 5. Thermal Protector:** Meets NEC and U.L. requirements. Do not install insulation within 3 inches of fixture sides or wiring compartment nor above fixture in such a manner as to entrap heat.

Labels

UL (Suitable for Damp Locations)

Romex® is a registered trademark of General Cable Industries Inc.

