

270° 200 WATT PAR MOTION-ACTIVATED SECURITY FLOODLIGHT



FEATURES

- Motion sensor detects motion 270° up to 90 ft.
- Die-cast metal housing with decorative lamp covers
- Combines Doppler radar with traditional PIR technology
- Detects lateral movement plus movement towards and away from the home
- Perfect for wall-mount or eave-mount applications
- Two 100W (maximum) PAR bulbs sold separately
- Available in bronze (MS276RD) and white (MS276RDW)

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed, RoHS Compliant




MS276RD SERIES
PRECISION PLUS
DOPPLER RADAR

ALTERNATE COLOR



MS276RDW White

100W PAR BULB



ORDERING INFORMATION

Model	Description	Unit Carton Dimension (Inches)	Unit Carton Weight (Pounds)	Master Carton Dimension (Inches)	Master Carton Weight (Pounds)	Master Carton Quantity
MS276RD	270° 200W PAR with Reflectors - Bronze	11.4H x 6.7W x 5.4D	2.20	12.0H x 7.2W x 11.4D	5.20	2
MS276RDW	270° 200W PAR with Reflectors - White	11.4H x 6.7W x 5.4D	2.20	12.0H x 7.2W x 11.4D	5.20	2

270° 200 WATT QUARTZ HALOGEN MOTION-ACTIVATED SECURITY FLOODLIGHT



FEATURES

- Motion sensor detects motion 270° up to 90 ft.
- Heavy-duty, die-cast metal rectangular twin head design
- Combines Doppler radar with traditional PIR technology
- Detects lateral movement plus movement towards and away from the home
- Perfect for wall-mount or eave-mount applications
- Two 100W (maximum) halogen bulbs included
- Available in bronze (MS280D) and white (MS280DW)

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed, RoHS Compliant




MS280D SERIES
PRECISION PLUS
DOPPLER RADAR

ALTERNATE COLOR



MS280DW White

100W HALOGEN BULB



ORDERING INFORMATION

Model	Description	Unit Carton Dimension (Inches)	Unit Carton Weight (Pounds)	Master Carton Dimension (Inches)	Master Carton Weight (Pounds)	Master Carton Quantity
MS280D	270° 200W Halogen - Bronze	6.8H x 12.1W x 6.9D	2.60	7.6H x 12.6W x 13.8D	6.10	2
MS280DW	270° 200W Halogen - White	6.8H x 12.1W x 6.9D	2.60	7.6H x 12.6W x 13.8D	6.10	2

270° 200 WATT PAR MOTION-ACTIVATED SECURITY FLOODLIGHT



FEATURES

- Motion sensor detects motion 270° up to 70 ft.
- Heavy-duty, die-cast metal housing construction
- Metal lamp covers provide maximum bulb protection
- Perfect for wall-mount or eave-mount applications
- Two 100W (maximum) PAR bulbs sold separately
- Available in bronze (MS245R) and white (MS245RW)

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed, RoHS Compliant




MS245R SERIES

ALTERNATE COLOR



MS245RW White

100W PAR BULB



ORDERING INFORMATION

Model	Description	Unit Carton Dimension (Inches)	Unit Carton Weight (Pounds)	Master Carton Dimension (Inches)	Master Carton Weight (Pounds)	Master Carton Quantity
MS245R	270° PAR - Bronze	11.5H x 6.8W x 5.0D	2.25	11.8H x 10.3W x 7.0D	5.00	2
MS245RW	270° PAR - White	11.5H x 6.8W x 5.0D	2.25	1.8H x 10.3W x 7.3D	5.00	2

NOTE: Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit our website at www.cooperlighting.com for available options, accessories and ordering information.