

# PHILIPS

Candle & Lustre

LED

2.1W-25W

E14

Warm White



8718699783334



## Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High-quality light

- Designed for the comfort of your eyes

### Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

### Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Replaces lustre incandescents

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Specifications

## Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E14
- Technology: LED
- Type of glass: Clear

## Lamp dimensions

- Height: 9 cm
- Weight: 0.014 kg
- Width: 2.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

## Light characteristics

- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Light Colour Category: Warm White
- Nominal luminous flux: 250 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 25 mA
- Efficacy: 119 lm/W

## Packaging information

- EAN: 8718699783334
- EOC: 871869978333400
- Product title: LED classic 25W T25L E14 CL ND RF 1PF/12

## Power consumption

- Power factor: 0.41
- Voltage: 220-240 V
- Wattage: 2.1 W
- Wattage equivalent: 25 W
- Energy efficiency label (EEL): E

## Product dimensions and weight

- Length: 9 cm

## Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 250 lm
- Rated power: 2.1 W

## Technical specifications

- Frequency: 50-60 Hz

The bulb

• Colour consistency: 6



Issue date: 2023-11-07  
Version: 0.421

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)