

PHILIPS

Tap dial switch

Hue

Wireless installation

Battery powered

Easy access to light scenes

Use as a remote control



8719514441057



Easy smart lighting

Control up to three Rooms or a Zone with each individual button of the Tap dial switch, available in black or white. Turn the dial to dim and brighten the lights. Mount it to the wall, place it on a magnetic surface, or use it as a remote control.

Full control from smart device with Hue bridge

- Control it your way

Hue switches 2022 convenience

- Convenient versatility

Hue switches 2022 control

- Set scenes instantly
- Use it your way
- Rotate to dim and brighten easily
- Use as a remote or mount to the wall

Highlights

Control it your way




Connect your Philips Hue lights with the bridge and start discovering the endless possibilities. Control your lights from your smartphone or tablet via the Philips Hue app, or add switches to your system to activate your lights. Set timers, notifications, alarms, and more for the full Philips Hue experience. Philips Hue even works with Amazon Alexa, Apple HomeKit and Google Home to allow you to control your lights with your voice.

Convenient versatility



Control your entire smart lighting system from anywhere in your home — without your phone or tablet.

Set scenes instantly



With a sleek, matte design in both black and white, the Philips Hue Tap dial switch lets you set scenes in any room of your home. Program each button to control 3 separate Rooms or a Zone — and choose a scene for each.

Use it your way



Mount the Tap dial switch to the wall with its adhesive backing, attach it to any magnetic surface, or remove it from the wall plate and use anywhere in your home as a remote control.

Rotate to dim and brighten easily



For precise lighting levels, turn the dial slowly to dim or brighten in smaller increments. Turn it faster to quickly brighten or dim the room.

Use as a remote or mount to the wall



Attach the Tap dial switch to the wall with its adhesive backing, place on any magnetic surface, or simply remove it from the wall plate to use as a remote control.

Specifications

Design and finishing

- Color: White
- Material: Synthetic

Environmental

- Operational humidity: 0%<H<80% (non condensing)
- Operational temperature: 0°C - 40°C

Extra feature/accessory incl.

- Portable: Yes

Guarantee

- 2 years: Yes

Packaging information

- EAN: 8719514441057

Product dimensions and weight

- Net weight: 0.07 kg
- Height: 2 cm
- Length: 6 cm
- Width: 6 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Number of configurable buttons: 4
- Battery type: CR - Button cell
- Class of protection: Class III

The switch

- Batteries included: 1 x CR2032
- Configurable buttons: 4 buttons and 1 dial
- Frequency band: 2400 - 2483.5 MHz
- IP rating: IP20
- Lifetime: 50.000 clicks / 12.000 turns
- Max. lights per switch: Not applicable
- Minimal battery lifetime: 2 year(s)
- Mounting options: freestanding, wall
- Software upgradeable: when connected to Hue bridge
- Wall plate depth: 6 mm
- Wall plate height: 125 mm
- Wall plate width: 80 mm

What's in the box

- Hue dimmer switch: n/a

What's supported

- HomeKit compatible: Yes
- Philips Hue App: IOS 15 and above, Android 10.0 and above

Packaging dimensions and weight

- EAN/UPC - product: 8719514441057
- Net weight: 0.1 kg
- Gross weight: 0.17 kg
- Height: 174 mm
- Length: 86 mm
- Width: 72 mm
- Material number (12NC): 929003500302



Issue date: 2024-02-02
Version: 0.144

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com