



High Output T12

F96T12/CW/HO-O ALTO 8/2PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	R17d (RDC)
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Luminous Flux	8,800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62
Operating and Electrical	
Power Consumption	110 W
Mechanical and Housing	
Bulb Shape	T-12


Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	110W T12 Cool White Tubular Fluorescent
Full product name	F96T12/CW/HO-O ALTO 8/2PK
Order code	205443
Material Nr. (12NC)	927895203339
Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.442 kg
EAN/UPC - Product/Case	046677205447
Numerator - Packs per outer box	8
EAN/UPC - Case	50046677205442

High Output T12

Dimensional drawing

Product

110W T12 Cool White Tubular Fluorescent



T12 Recessed Double Contact

