



# MASTER PL-L 4 Pin

## 36 W 4 Pin Cool white Non integrated compact fluorescent

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	2G11
Nominal lifetime	15,000 h
Life to 50% Failures (Nom)	15,000 h
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,900 lm
Color Designation	Cool White (CW)
Luminous Efficacy (rated) (Nom)	81 lm/W
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	36.0 W

Lamp Current (Nom)	0.435 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	40 kWh
Product Data	
Order product name	36 W 4 Pin Cool white Non integrated compact fluorescent
Full product name	36 W 4 Pin Cool white Non integrated compact fluorescent
Full product code	871150070675141
Order code	927903408472

MASTER PL-L 4 Pin

Material Nr. (12NC)	927903408472
Numerator - Quantity Per Pack	1
Net Weight (Piece)	104.000 g
EAN/UPC - Product/Case	8711500706751


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500711014

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
36 W 4 Pin Cool white Non integrated compact fluorescent	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/840/4P 1CT/25

