



MASTER PL-L 4 针

36 W 4 Pin Cool daylight Non integrated compact fluorescent

紧凑型节能荧光灯。紧凑的长弧结构，低压低汞荧光灯管。由 2 根平行的细荧光灯管组成

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	2G11
标称使用寿命	15,000 小时
50% 故障条件下的使用寿命 (标称)	15,000 小时

灯技术	
颜色代码	865 [CCT of 6500K]
光通量	2,900 lm
光效 (额定)(标称)	80 lm/W
颜色名称	冷日光
相关色温 (标称)	6500 K
显色指数 (CRI)	80

操作和电气	
功耗	36 W
灯具电流 (标称)	0.435 A

控制和调光	
可调光	是


审批和申请	
汞 (Hg) 含量 (标称)	2.0 mg
能耗 kWh/1000 h	40 kWh

产品数据	
订单产品名称	36 W 4 Pin Cool daylight Non integrated compact fluorescent
完整的产品名称	36 W 4 Pin Cool daylight Non integrated compact fluorescent
完整产品代码	871150063520441
订购代码	927903486572
材料编号 (12NC)	927903486572
计算器 - 每包数量	1
净重 (每件)	104.000 g

MASTER PL-L 4 针


EAN/UPC - 产品/箱	8711500635204
计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	8711500635211

二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
36 W 4 Pin Cool daylight Non integrated compact fluorescent	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

光度数据



Spectral Power Distribution Colour - MASTER PL-L 36W/865/4P 1CT/25

