



# MASTER PL-C 4 Pin

## 26 W 4 Pin Cool white Non integrated compact fluorescent

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

| General Information                |                    | Operating and Electrical      |         |
|------------------------------------|--------------------|-------------------------------|---------|
| Cap-Base                           | G24q-3             | Power Consumption             | 26.0 W  |
| Nominal lifetime                   | 10,000 hour(s)     | Lamp Current (Nom)            | 0.335 A |
| Light Technical                    |                    | Controls and Dimming          |         |
| Color Code                         | 840 [CCT of 4000K] | Dimmable                      | Yes     |
| Luminous Flux                      | 1,800 lm           | Approval and Application      |         |
| Luminous Efficacy (rated) (Nom)    | 67 lm/W            | Mercury (Hg) Content (Nom)    | 1.4 mg  |
| Color Designation                  | Cool White (CW)    | Energy Consumption kWh/1000 h | 29 kWh  |
| Correlated Color Temperature (Nom) | 4000 K             |                               |         |
| Color rendering index (CRI)        | 82                 |                               |         |


# MASTER PL-C 4 Pin

## Product Data

|                     |  |
|---------------------|--|
| Order product name  | 26 W 4 Pin Cool white Non integrated compact fluorescent |
| Full product name   | 26 W 4 Pin Cool white Non integrated compact fluorescent |
| Full product code   | 871150062336200  |
| Order code          | 927907384002   |
| Material Nr. (12NC) | 927907384002   |


|                                 |               |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack   | 1             |
| Net Weight (Piece)              | 60.400 g      |
| EAN/UPC - Product/Case          | 8711500623362 |
| Numerator - Packs per outer box | 50            |
| EAN/UPC - Case                  | 8711500716057 |

## Dimensional drawing



| Product  | D (max) | D1 (max) | A (max)  | B (max)  | C (max)  |
|--|---------|----------|----------|----------|----------|
| 26 W 4 Pin Cool white Non integrated compact fluorescent | 27.1 mm | 27.1 mm  | 130.5 mm | 149.0 mm | 163.9 mm |

## Photometric data



Spectral Power Distribution Colour - MASTER PL-C 26W/840/4P 1CT/5X10BOX


# MASTER PL-C 4 Pin

## Lifetime



Life expectancy diagram - 3 hour cycle

Life expectancy diagram - 12 hour cycle



Lumen Maintenance Diagram - MASTER PL-C 26W/840/4P 1CT/5X10BOX

