



# MASTER PL-L 4 针

## 55 W 4 Pin Cool daylight Non integrated compact fluorescent

紧凑型节能荧光灯。紧凑的长弧结构，低压低汞荧光灯管。由 2 根平行的细荧光灯管组成

### 安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据

一般信息	
底盖	2G11
标称使用寿命	15,000 小时

灯技术	
颜色代码	865 [CCT of 6500K]
光通量	4,600 lm
光效 (额定) (标称)	82 lm/W
颜色名称	冷日光
相关色温 (标称)	6500 K
显色指数 (CRI)	80

操作和电气	
功耗	55.0 W
灯具电流 (标称)	0.525 A

控制和调光	
可调光	是

审批和申请	
汞 (Hg) 含量 (标称)	2.0 mg
能耗 kWh/1000 h	61 kWh


  

产品数据	
订单产品名称	55 W 4 Pin Cool daylight Non integrated compact fluorescent
完整的产品名称	55 W 4 Pin Cool daylight Non integrated compact fluorescent
完整产品代码	871150026170041
订购代码	927908786572
材料编号 (12NC)	927908786572
计算器 - 每包数量	1
净重 (每件)	134.000 g

# MASTER PL-L 4 针


EAN/UPC - 产品/箱	8711500261700
计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	8711500261717

## 二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
55 W 4 Pin Cool daylight Non integrated compact fluorescent	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

## 光度数据



Spectral Power Distribution Colour - MASTER PL-L 55W/865/4P 1CT/25

