



TL-D LIFEMAX Super 80

18 W G13 Cool white Linear fluorescent tube

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

Informasi Umum		Mekanis dan Housing	
Tutup-Dasar	G13 [Medium Bi-Pin Fluorescent]	Bentuk Bohlam	T8
Nominal masa pakai	15.000 jam		
Masa Pakai hingga 50 % Kegagalan (Nom)	13.000 jam		
Teknis Lampu		Penyetujuan dan Aplikasi	
Kode Warna	840 [CCT of 4000K]	Kandungan Merkuri (Hg) (Nom)	2,0 mg
Penandaan Warna	Cool White (CW)		
Daya Penerangan (terukur) (Nom)	75 lm/W	Data Produk	
Suhu Warna Terkorelasi (Nom)	4000 K	Nama produk pesanan	18 W G13 Cool white Linear fluorescent tube
Indeks renderasi warna (CRI)	82	Nama lengkap produk	18 W G13 Cool white Linear fluorescent tube
Pengoperasian dan Kelistrikan		Kode produk lengkap	871150028560700
Konsumsi Daya	18 W	Kode urutan	927980284036
Arus Lampu (Nom)	0,360 A	No. Material (12NC)	927980284036
Tegangan (Nom)	59 V	Numerator - Jumlah Per Pak	1
Kontrol dan Peredupan		Berat Bersih (Bagian)	0,070 kg
Dapat diredupkan	Ya	EAN/UPC - Produk/Kantung	8711500285607
		Numerator - Pak per kotak bagian luar	25
		EAN/UPC - Kantung	8711500285812



TL-D LIFEMAX Super 80

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
18 W G13 Cool white Linear fluorescent tube	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Lifetime



Life expectancy diagram - 3 hour cycle

Life expectancy diagram - 12 hour cycle



Lumen Maintenance Diagram - TL-D 18W/840 1SL/25

TL-D LIFEMAX Super 80

