



# TL-D LIFEMAX Super 80

## 18 W G13 Cool daylight Linear fluorescent tube

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Product data

Informasi Umum	
Tutup-Dasar	G13 [Medium Bi-Pin Fluorescent]
Nominal masa pakai	15.000 jam
Masa Pakai hingga 50 % Kegagalan (Nom)	13.000 jam

Teknis Lampu	
Kode Warna	865 [CCT of 6500K]
Penandaan Warna	Cool Daylight
Daya Penerangan (terukur) (Nom)	71 lm/W
Suhu Warna Terkorelasi (Nom)	6500 K
Indeks renderasi warna (CRI)	80

Pengoperasian dan Kelistrikan	
Konsumsi Daya	18 W
Arus Lampu (Nom)	0,360 A
Tegangan (Nom)	59 V

Kontrol dan Peredupan	
Dapat diredupkan	Ya

Mekanis dan Housing	
Bentuk Bohlam	T8

Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	2,0 mg

Data Produk	
Nama produk pesanan	18 W G13 Cool daylight Linear fluorescent tube
Nama lengkap produk	18 W G13 Cool daylight Linear fluorescent tube
Kode produk lengkap	871150028562100
Kode urutan	927980286536
No. Material (12NC)	927980286536
Numerator - Jumlah Per Pak	1
Berat Bersih (Bagian)	0,070 kg
EAN/UPC - Produk/Kantung	8711500285621
Numerator - Pak per kotak bagian luar	25
EAN/UPC - Kantung	8711500285836


# TL-D LIFEMAX Super 80

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
18 W G13 Cool daylight Linear fluorescent tube	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

## Photometric data




Spectral Power Distribution Colour - TL-D 18W/865 1SL/25

## Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

## TL-D LIFEMAX Super 80

### Lifetime



Lumen Maintenance Diagram - TL-D 18W/865 1SL/25

