



TL-D LIFEMAX Super 80

30 W G13 Cool white Linear fluorescent tube

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	15,000 hour(s)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Color Designation	Cool White (CW)
Luminous Efficacy (rated) (Nom)	80 lm/W
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	30 W
Lamp Current (Nom)	0.360 A
Voltage (Nom)	98 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	30 W G13 Cool white Linear fluorescent tube
Full product name	30 W G13 Cool white Linear fluorescent tube
Full product code	871150028588100
Order code	927981284036
Material Nr. (12NC)	927981284036
Local order code	TLD30W840
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.130 kg
EAN/UPC - Product/Case	8711500285881
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500285904



TL-D LIFEMAX Super 80

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
30 W G13 Cool white Linear fluorescent tube	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

Lifetime



Life expectancy diagram - 3 hour cycle

Life expectancy diagram - 12 hour cycle



Lumen Maintenance Diagram - TL-D 30W/840 1SL/25

TL-D LIFEMAX Super 80

