



Retail Sales T8

F15T8/COOL WHITE PLUS/18 ALTO 6PK

Energy Savings, extra long life, extra low mercury. T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Warnings and Safety


- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	33-640
Luminous Flux	830 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	63
Operating and Electrical	
Power Consumption	15 W
Lamp Current (Nom)	0.335 A
Wattage Equivalent	15 W
Voltage (Nom)	55 V


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	15W T8 Cool White Tubular Fluorescent
Full product name	F15T8/COOL WHITE PLUS/18 ALTO 6PK
Order code	392076
Material Nr. (12NC)	928022803328
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.131 lb
EAN/UPC - Product/Case	046677392079
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677392074

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
15W T8 Cool White Tubular Fluorescent	1-1/8 inch	17-1/4 inch	17-1/2 inch	17-7/16 inch	17-13/16 inch

Photometric data




Spectral Power Distribution Colour - F15T8/COOL WHITE PLUS/18 ALTO SL 6

Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

Lifetime



Lumen Maintenance Diagram - F15T8/COOL WHITE PLUS/18 ALTO SL 6

