



TL-E LIFEMAX

Standard Colours

22 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.


Product data

Informasi Umum	
Tutup-Dasar	G10q
Nominal masa pakai	8.000 jam
Masa Pakai hingga 50 % Kegagalan (Nom)	13.000 jam
Teknis Lampu	
Kode Warna	54-765
Flux Cahaya	1.050 lm
Penandaan Warna	Cool Daylight
Daya Penerangan (terukur) (Nom)	48 lm/W
Suhu Warna Terkorelasi (Nom)	6200 K
Indeks renderasi warna (CRI)	72
Pengoperasian dan Kelistrikan	
Konsumsi Daya	22,0 W
Arus Lampu (Nom)	0.400 A
Tegangan (Nom)	62 V
Kontrol dan Peredupan	
Dapat diredupkan	Ya

Mekanis dan Housing	
Bentuk Bohlam	C-T29
Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	9 mg
Data Produk	
Nama produk pesanan	22 W G10q Cool daylight Circular fluorescent
Nama lengkap produk	22 W G10q Cool daylight Circular fluorescent
Kode produk lengkap	871150063390300
Kode urutan	928026205436
No. Material (12NC)	928026205436
Numerator - Jumlah Per Pak	1
Berat Bersih (Bagian)	0,110 kg
EAN/UPC - Produk/Kantung	8711500633903
Numerator - Pak per kotak bagian luar	20
EAN/UPC - Kantung	8711500633910


TL-E LIFEMAX Standard Colours

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
22 W G10q Cool daylight Circular fluorescent	30,9 mm	26,2 mm	205,0 mm	213,5 mm	149,1 mm	155,6 mm

Photometric data



Spectral Power Distribution Colour - TL-E 22W/54-765 1CT/20

