



TL-E LIFEMAX

Standard Colours

32 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.


Product data

General Information	
Cap-Base	G10q
Nominal lifetime	8,000 hour(s)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	1,750 lm
Luminous Efficacy (rated) (Nom)	57 lm/W
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	32.0 W
Lamp Current (Nom)	0.450 A
Voltage (Nom)	81 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	C-T29
Approval and Application	
Mercury (Hg) Content (Nom)	9 mg
Product Data	
Order product name	32 W G10q Cool daylight Circular fluorescent
Full product name	32 W G10q Cool daylight Circular fluorescent
Full product code	871150063387301
Order code	928026305436
Material Nr. (12NC)	928026305436
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.180 kg
EAN/UPC - Product/Case	8711500633873
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500633880


TL-E LIFEMAX Standard Colours

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
32 W G10q Cool daylight Circular fluorescent	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

Photometric data



Spectral Power Distribution Colour - TL-E 32W/54-765 1CT/20

