



TL-E LIFEMAX

Standard Colours

32 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.


Product data

Informasi Umum	
Tutup-Dasar	G10q
Nominal masa pakai	8.000 jam
Masa Pakai hingga 50 % Kegagalan (Nom)	13.000 jam
Teknis Lampu	
Kode Warna	54-765
Flux Cahaya	1.750 lm
Penandaan Warna	Cool Daylight
Daya Penerangan (terukur) (Nom)	57 lm/W
Suhu Warna Terkorelasi (Nom)	6200 K
Indeks renderasi warna (CRI)	72
Pengoperasian dan Kelistrikan	
Konsumsi Daya	32,0 W
Arus Lampu (Nom)	0.450 A
Tegangan (Nom)	81 V
Kontrol dan Peredupan	
Dapat diredupkan	Ya

Mekanis dan Housing	
Bentuk Bohlam	C-T29
Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	9 mg
Data Produk	
Nama produk pesanan	32 W G10q Cool daylight Circular fluorescent
Nama lengkap produk	32 W G10q Cool daylight Circular fluorescent
Kode produk lengkap	871150063387301
Kode urutan	928026305436
No. Material (12NC)	928026305436
Numerator - Jumlah Per Pak	1
Berat Bersih (Bagian)	0,180 kg
EAN/UPC - Produk/Kantung	8711500633873
Numerator - Pak per kotak bagian luar	20
EAN/UPC - Kantung	8711500633880


TL-E LIFEMAX Standard Colours

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
32 W G10q Cool daylight Circular fluorescent	30,9 mm	27,1 mm	299,0 mm	303,5 mm	241,0 mm	246,0 mm

Photometric data



Spectral Power Distribution Colour - TL-E 32W/54-765 1CT/20

