

PHILIPS

Lighting

MASTER TL-E Circular Super 80

32 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

安全提示

· A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息		电压 (标称)		81 V	
底盖	G10q				
标称使用寿命	8,000 小时				
50% 故障条件下的使用寿命 (标称)	13,000 小时				
灯技术		控制和调光			
颜色代码	865 [CCT of 6500K]	可调光	是		
光通量	2,310 lm				
光效 (额定) (标称)	72 lm/W				
颜色名称	冷日光				
相关色温 (标称)	6500 K				
显色指数 (CRI)	80				
操作和电气		机械和外壳			
功耗	32.0 W	灯泡外形	C-T29		
灯具电流 (标称)	0.450 A				
		审批和申请			
		汞 (Hg) 含量 (标称)	8 mg		
		能耗 kWh/1000 h	35 kWh		
		产品数据			
		订单产品名称	32 W G10q Cool daylight Circular fluorescent		
		完整的产品名称	32 W G10q Cool daylight Circular fluorescent		
		完整产品代码	871150064038300		

MASTER TL-E Circular Super 80

订购代码	928026386574
材料编号 (12NC)	928026386574
计算器 - 每包数量	1
净重 (每件)	0.110 kg
EAN/UPC - 产品/箱	8711500640383

计算器 - 每个外包装箱中的包数	20
EAN/UPC - 案例	8727900813616

二维绘图



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
32 W G10q Cool daylight Circular fluorescent	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

