



# Ecofit Ledtubes T8

## 8W (18W) G13 Cool White Non-dimmable Linear tube

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

### Product data

General Information		Power Consumption	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	8 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)	0.5
Lighting Technology	LED	Voltage (Nom)	220-240 V
		Ballast Compatibility	EM
Light Technical		Temperature	
Color Code	740 [CCT of 4000K]	Ambient temperature range	-20 °C to 45 °C
Beam Angle (Nom)	240 degree(s)	T-Case Maximum (Nom)	60 °C
Luminous Flux	800 lm		
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K		
Color Consistency	<7	Mechanical and Housing	
Color rendering index (CRI)	73	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
		Product Length	600 mm
		Bulb Shape	T8
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

# Ecofit Ledtubes T8

## Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

## Product Data



Order product name	8W (18W) G13 Cool White Non-dimmable Linear tube
--------------------	-----------------------------------------------------

Full product name	8W (18W) G13 Cool White Non-dimmable Linear tube
Full product code	871869652505000
Order code	929001184708
Material Nr. (12NC)	929001184708
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.090 kg
EAN/UPC - Product/Case	8718696525050
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696525067

## Dimensional drawing

Product	D1	D2	A1	A2	A3	C	D
8W (18W) G13 Cool White Non- dimmable Linear tube	25.68 mm	28 mm	588.5 mm	595.5 mm	602.5 mm	602.5 mm	27.8 mm

## Photometric data




General uniform lighting - LEDtube 600mm 8W 740 T8 AP C G

Light Distribution Diagram - LEDtube 600mm 8W 740 T8 AP C G


# Ecofit Ledtubes T8

## Photometric data




Spectral Power Distribution Colour - LEDtube 600mm 8W 740 T8 AP C G


## Lifetime




LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G




LEDtube 16W G13 740 T8 AP I G



Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP C G

## Ecofit Ledtubes T8

### Lifetime



Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP C G

