



Ecofit Ledtubes T8

8W (18W) G13 Cool White Non-dimmable Linear tube

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information		Power Consumption	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	8 W
Nominal lifetime	15000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	15000 hour(s)	Power Factor (Fraction)	0.5
Lighting Technology	LED	Voltage (Nom)	220-240 V
		Ballast Compatibility	EM
Light Technical		Temperature	
Color Code	740 [CCT of 4000K]	Ambient temperature range	-20 °C to 45 °C
Beam Angle (Nom)	240 degree(s)	T-Case Maximum (Nom)	60 °C
Luminous Flux	800 lm		
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K		
Color Consistency	<7	Mechanical and Housing	
Color rendering index (CRI)	73	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
		Product Length	600 mm
		Bulb Shape	T8
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Ecofit Ledtubes T8

Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

Product Data



Order product name	8W (18W) G13 Cool White Non-dimmable Linear tube
--------------------	---

Full product name	8W (18W) G13 Cool White Non-dimmable Linear tube
Full product code	871869652505000
Order code	929001184708
Material Nr. (12NC)	929001184708
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.090 kg
EAN/UPC - Product/Case	8718696525050
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696525067

Dimensional drawing

Product	D1	D2	A1	A2	A3	C	D
8W (18W) G13 Cool White Non- dimmable Linear tube	25.68 mm	28 mm	588.5 mm	595.5 mm	602.5 mm	602.5 mm	27.8 mm

Photometric data




General uniform lighting - LEDtube 600mm 8W 740 T8 AP C G

Light Distribution Diagram - LEDtube 600mm 8W 740 T8 AP C G


Ecofit Ledtubes T8

Photometric data




Spectral Power Distribution Colour - LEDtube 600mm 8W 740 T8 AP C G


Lifetime




LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G




LEDtube 16W G13 740 T8 AP I G



Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP C G

Ecofit Ledtubes T8

Lifetime



Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP C G

