

# Ecofit Ledtubes T8

## LEDtube 600mm 8W 765 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

### Product data

General Information		Power Consumption	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	8 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)	0.5
Lighting Technology	LED	Voltage (Nom)	220-240 V
EU RoHS compliant	Yes	<b>Temperature</b>	
<b>Light Technical</b>		Ambient temperature range	-20 °C to 45 °C
Color Code	765 [CCT of 6500K]	T-Case Maximum (Nom)	60 °C
Beam Angle (Nom)	240 degree(s)	<b>Controls and Dimming</b>	
Luminous Flux	800 lm	Dimmable	No
Color Designation	Cool Daylight	<b>Mechanical and Housing</b>	
Correlated Color Temperature (Nom)	6500 K	Bulb Finish	Frosted
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Bulb Material	Glass
Color Consistency	<7	Product Length	600 mm
Color rendering index (CRI)	73	Bulb Shape	T8
LLMF At End Of Nominal Lifetime (Nom)	70 %	<b>Approval and Application</b>	
<b>Operating and Electrical</b>		Energy Saving Product	Yes
Line Frequency	50 to 60 Hz	Suitable For Accent Lighting	No
Input Frequency	50 to 60 Hz		

# Ecofit Ledtubes T8



Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EyeComfort	Yes
<b>Product Data</b>	
Order product name	LEDtube 600mm 8W 765 T8 AP C G
Full product name	LEDtube 600mm 8W 765 T8 AP C G
Full product code	871869652507400

Order code	929001184808
Material Nr. (12NC)	929001184808
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696525074
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696525081

## Dimensional drawing


Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28 mm	588.5	595.5	602.5	602.5	27.8
8W 765 T8 AP C G	mm		mm	mm	mm	mm	mm

## Photometric data



General uniform lighting - LEDtube 600mm 8W 765 T8 AP C G



Light Distribution Diagram - LEDtube 600mm 8W 765 T8 AP C G




Spectral Power Distribution Colour - LEDtube 600mm 8W 765 T8 AP C G

# Ecofit Ledtubes T8


## Lifetime




Life Expectancy Diagram - LEDtube 600mm 8W 765 T8 AP C G



Life Expectancy Diagram - LEDtube 600mm 8W 765 T8 AP C G



Life Expectancy Diagram - LEDtube 600mm 8W 765 T8 AP C G



Lumen Maintenance Diagram - LEDtube 600mm 8W 765 T8 AP C G

Lumen Maintenance Diagram - LEDtube 600mm 8W 765 T8 AP C G

## Ecofit Ledtubes T8

