



Party Spot

13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF

Philips 13.5-watt PAR 38s provide bright colorful light perfect for special occasions, parties and holidays. These PAR 38 lamps are available in up to four different colors and offer a festive touch to your home lighting. Brighten up your home and celebrate with color using these energy saving LED bulbs.

Product data

General Information		UL Type	
Cap-Base	E26 [Single Contact Medium Screw]	UL Type	Yes
Nominal lifetime	10,950 hour(s)	Temperature	
Switching Cycle	10,000	Ambient temperature range	-4 °F to 113 °F
Rated Lifetime (Hours)	10,950 hour(s)	T-Case Maximum (Nom)	149 °F
Lighting Technology	LED	Controls and Dimming	
Light Technical		Dimmable	No
Color Code	Red	Mechanical and Housing	
Color Designation	Red	Bulb Finish	Frosted
Color Consistency	<6	Bulb Material	Glass
Color rendering index (CRI)	-	Bulb Shape	PAR38
LLMF At End Of Nominal Lifetime (Nom)	70 %	UL Wet/ damp/ dry location	Wet location
Operating and Electrical		Approval and Application	
Line Frequency	60 Hz	Suitable For Accent Lighting	Yes
Input Frequency	60 Hz	EU RoHS compliant	Yes
Power Consumption	13.5 W	EyeComfort	Yes
Lamp Current (Nom)	165 mA	T20 compliant	N/A
Starting Time (Nom)	0.5 s	LED Innovations	EyeComfort
Warm-up time to 60% light	0.5 s		
Power Factor (Fraction)	0.5		
Voltage (Nom)	120 V		

Party Spot

Application Conditions


can it be used in closed luminaires Yes

Product Data

Order product name	13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF
Full product name	13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF
Order code	568295
Material Nr. (12NC)	929001306863



Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.772 lb
EAN/UPC - Product/Case	046677568290
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677568295

Dimensional drawing



Product	D	C
13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF	4-13/16 inch	5-1/4 inch

Photometric data




Accent Lighting Spots - 13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF

Light Distribution Diagram - 13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF

Party Spot

Lifetime



Lumen Maintenance Diagram - 13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF

Life Expectancy Diagram

