



Classic filament LEDbulbs

LED classic 60W G93 E27 WW CL ND 1PF

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes

Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	115.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1

Stroboscopic effect	0.4
---------------------	-----

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	7 W
Lamp current (nom.)	60 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	45 °C

Controls and Dimming	
Dimmable	No

Classic filament LEDbulbs

Mechanical and Housing

Lamp Finish	Clear
Bulb shape	G93 [G 93 mm]

Approval and Application


Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	7 kWh
EPREL registration number	400289
EyeComfort	Yes

Product Data

Order product name	LED classic 60W G93 E27 WW CL ND 1PF
--------------------	--------------------------------------



Full product name	LED classic 60W G93 E27 WW CL ND 1PF
Full EOC	871869674245700
Order code	74245700
Material no. (12 NC)	929001387901
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696742457
Numerator – packs per outer box	4
EAN/UPC – Case	8718696742464

Dimensional drawing



Product	D	C
LED classic 60W G93 E27 WW CL ND 1PF	95 mm	140 mm

Photometric data




General uniform lighting - LED classic 60W G93 E27 WW CL ND 1PF

Spectral Power Distribution Colour - LED classic 60W G93 E27 WW CL ND 1PF


Classic filament LEDbulbs

Photometric data




Light Distribution Diagram - LED classic 60W G93 E27 WW CL ND 1PF

Lifetime



Life Expectancy Diagram - LED classic 60W G93 E27 WW CL ND 1PF



Lumen Maintenance Diagram - LED classic 60W G93 E27 WW CL ND 1PF

