



# Classic filament LED candles and lustres

## LEDClassic CM P45 35W WW E14 CL ND SRT4

Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.

### Product data

General Information	
Cap base	E14 [E14]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Colour Code	827 [CCT of 2700K]
Colour Code	827 [CCT of 2700K]
Luminous Flux	397 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	99.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1

Stroboscopic effect	0.4
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	4 W
Lamp current (nom.)	40 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.41
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	45 °C
Controls and Dimming	
Dimmable	No

# Classic filament LED candles and lustres

## Mechanical and Housing

Lamp Finish	Mirror Crown
Bulb shape	P45 [P 45 mm]

## Approval and Application


Energy Efficiency Class	F
Energy consumption kWh/1,000 hours	4 kWh
EPREL registration number	387397
EyeComfort	Yes

## Product Data

Order product name	LEDClassic CM P45 35W WW E14 CL ND SRT4
--------------------	-----------------------------------------



Full product name	LEDClassic CM P45 35W WW E14 CL ND SRT4
Full EOC	871869976351000
Order code	76351000
Material no. (12 NC)	929001395155
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699763510
Numerator – packs per outer box	4
EAN/UPC – Case	8718699763527

## Dimensional drawing



Product	D	C
LEDClassic CM P45 35W WW E14 CL ND SRT4	45 mm	82 mm

## Photometric data




General uniform lighting - LEDClassic CM P45 35W WW E14 CL ND SRT4

Spectral Power Distribution Colour - LEDClassic CM P45 35W WW E14 CL ND SRT4


# Classic filament LED candles and lustres

## Photometric data




Light Distribution Diagram - LEDClassic CM P45 35W WW E14 CL ND SRT4

## Lifetime



Life Expectancy Diagram - LEDClassic CM P45 35W WW E14 CL ND SRT4



Lumen Maintenance Diagram - LEDClassic CM P45 35W WW E14 CL ND SRT4

