



# Accessory

## CORD/classic/E27/gold 1CT EU RF

This Philips cable combines a fabric wire and metal socket with matt finishing to bring a vibe to your living space. Paired with a E27 LED bulb from the Philips vintage, modern or classic range to complete the look.

### Product data

General Information	
Cap base	E27
Nominal lifetime	10.950 h
Switching Cycle	25,000
Lighting Technology	LED

  

Light Technical	
Luminous efficacy (rated) (nom.)	0.00 lm/W

  

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	40 W
Lamp current (nom.)	330 mA
Warm-up time to 60% light	Instant full light s
Voltage (nom.)	120-240 V

  

Approval and Application	
CE mark	Yes

EU RoHS compliant	Yes
-------------------	-----

  

Application Conditions	
Can it be used in closed luminaires	No

  

Product Data	
Order product name	40W E27 Bulb
Full product name	CORD/classic/E27/gold 1CT EU RF
Full EOC	871869616777900
Order code	16777900
Material no. (12 NC)	929001978001
Numerator – quantity per pack	1
Net Weight (Piece)	0.432 kg
EAN/UPC – Product/Case	8718696167779
Numerator – packs per outer box	4
EAN/UPC - Case	8718699624101